

PT-D600VP

24mm Desktop Label Printer

High resolution colour LCD display

One Touch function key for ease of use

Includes AC adapter, USB cable
& 24mm Black on white Tze tape (4m)

Horizontal wide Qwerty keyboard



Top Features:

High resolution colour LCD display

- Easy-to-read text and the ability to preview your label before printing.

One look Edit

- Preview the label on-screen with the actual resolution that it will print
- Customer can see the whole label image as they edit
- TZe colour detection

PC Connectable

- Compatible with PT-Editor 5.1
- Windows & Mac drivers available

Horizontally wider PC style keyboard

- Easy to type like on a PC

High Speed Print

- 30mm/second print speed (Max)

Multiple power options

- Supplied with an AC adaptor . Also works with 6 AA batteries (not supplied)

Convenient and professional auto cutter

- Increased efficiency
- Prevents mis-cutting
- Precise cutting edge

High Print resolution

- This mode creates crisp text, graphics and barcode labels when you connect with your laptop.

General

Carton contents	PT-D600VP labelling machine 24mm TZe black on white 4m tape cassette AC adaptor Documentation USB-mini cable Carry case
Language support	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Brazilian Portuguese, Turkish

Dimensions & Weights

Without carton	206(w) x 192(d) x 86(h) † 0.95 kg
With carton	
Master carton	

Built In Features

Keyboard	62 Key Rubber QWERTY/QWERTZ/AZERTY
Dedicated number keypad	Yes
Interfaces	USB
Operating system support	Microsoft Windows® Vista, Windows® 7, Windows® 8, Mac OS/X 10.7 to 10.9.
Display type	Backlit High resolution Colour LCD with label preview capability
Display resolution	20 characters by 3 lines † 320 x 120 dots
Printing speed	Up to 30mm/second
Print resolution	180dpi (180 x 360 dpi in high resolution mode)
Maximum print height	18.0mm
Cutter type	Auto Full
Label length	30mm minimum † 300mm maximum
Maximum lines per label	7 (for 24mm wide tape)
Vertical text printing	Yes
Mirror printing	Yes
Copies	1 to 99
Numbering	Yes (9 times)

Label Creation

Fonts	14 † Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Calgary, Belgium, Atlanta, Adams, Brunei, Sofia, Germany, Letter Gothic
Font styles	10 (excl. Normal) † Normal, Bold, Outline, Shadow, Solid, Italic, Italic Bold, Italic Outline, Italic Shadow, Italic Solid, Vertical Bold
Font sizes	6, 9, 12, 18, 24, 36, 42, 48 point
Symbols	617
Frames	99
Barcodes	9 † CODE39, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128 (UCC/EAN128), CODE128

Memory

Max. characters per label	Max 2,800 characters
Label memory locations	99 areas

Supplies

Tape type	TZe
Tape widths	3.5, 6, 9, 12, 18 & 24mm

Optional Accessories

Batteries	AA alkaline/rechargeable batteries (LR6/HR6) x 6
AC adaptor	AD-E001