





Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 10M ohm Min.
4. Hi-Pot: 300VDC/10ms.



Pin Assignment

P1		P2
(4,9,16,21)(A4A9B4B9)	VBus	VBus
(A7) Dn1	White	Dn1
(A6) Dp1	Green	Dp1
(A5) CC	Yellow	CC
(1,12,13,24)(A1A12B1B12)	GND	GND
Shell	Braid	Shell

⑦	A0020100-00174	USB TYPE C~n DOWM Nickel Plated Shell	1	pcs	版本	ECN编号	描述		日期	变更人	
⑥	A0020100-00175	USB TYPE C~n UP Nickel Plated Shell~	1	pcs		TOLERANCE INCHES M/M		TITLE: USB2.0 CM TO CM CABLE L=1M			
⑤	A10-R075552	H.S TUBE Color:Black Ø:1.0 L=16mm*1pcs	0.016	M		. X	. 015				. 30
④	A5-R047001	Transparent PE	16	g		. XX	. 010				. 10
③	A5-R047011	45P PVC Color:Sonw BLACK	6	g		. XXX	. 005				. 05
②	B010-00875	USB 2.0 C Type Black Insulation Nickel Plated Shell NO With PCBA	1	pcs	DRAWN BY	李敏		CUSTOMER :	CPC		
①	A0010306-00986	NO~UL~23AWG (35/0. 10+250D NylonTC)*1C+32AWG (19/0. 05TC)*2C+32AWG (7/0. 08TC)*1C+3E (19/0. 1TC)+AB (16/9/0. 06TC 85%TC) OD: 3. 3MM~BLACK NO MARK	1	M	CHECK BY			SCALE	NONE	DRAWING NO. :	REV. A
					UNIT			mm	C06026-00013	1/1	
					DATE			2015.05.13			
					DESCRIPTION			DATE			