



AkroBins®

Industry-leading hanging and stacking bins!

- Heavy-duty bins stack, sit on shelving or hang from panels and rails
- Optional dividers allow you to create customizable compartment sizes



The new bin size, 30237, can be used back to back as a two-bin Kanban solution on 18" deep shelves!



30237

**NEW!
SIZE**

**MADE
IN THE
USA**



30250 with 40245CRY
Clear Length Divider

30260 with 40260
Length Divider

30230 with 41230
Width Dividers

30230 with
30231CRY Lid

30230 with 29230
Adhesive Label

40599 Bin
Retainer Clip

40412 Kanban
Extended
Label Holders
Turn your existing bin
inventory system into
a Kanban system

AkroBins Model No.	Outside Dimensions (In.)			Bottom Dimensions (In.)				Capacity/Quantity		Accessories							
	L	W	H	L	W	H	X	Bin Load Capacity On Rack	Bin Ctn. Qty.	Black Length Dividers†	Black Width Dividers†	Clear Length Dividers‡	Divider Pkg. Qty.	Bin Lids	Lid Pkg. Qty.	Adhesive Labels	Card Stock
30210* ^{SS}	5-3/8	4-1/8	3	4-3/4	3-7/16	2-13/16	4	10 lbs.	24	40210 (1)	–	40210CRY	6	30211CRY	24	29202	29301
30220* ^{SS}	7-3/8	4-1/8	3	6-3/4	3-7/16	2-13/16	6	10 lbs.	24	40220 (1)	–	40220CRY	6	30221CRY	24	29202	29301
30237	9-1/4	6	5	8-9/16	4-7/8	4-3/4	7-1/4	20 lbs.	12	40237 (1)	–	40237CRY	6	–	–	29203	29302
30224*	10-7/8	4-1/8	4	10-1/4	3-3/16	3-3/4	9	20 lbs.	12	40224 (1)	–	40224CRY	6	30225CRY	12	29202	29301
30230* ^{SS}	10-7/8	5-1/2	5	10-1/4	4-3/8	4-3/4	9	30 lbs.	12	40230 (1)	41230 (3)	40230CRY	6	30231CRY	12	29203	29302
30234* ^{SS}	14-3/4	5-1/2	5	14-1/16	4-3/8	4-3/4	12-13/16	50 lbs.	12	40234 (1)	–	40234CRY	6	–	–	29203	29302
30239* ^{SS}	10-3/4	8-1/4	7	10	6-9/16	6-3/4	8	50 lbs.	6	40239 (1)	–	40239CRY	6	–	–	29203	29302
30240* ^{SS}	14-3/4	8-1/4	7	14	6-9/16	6-3/4	12	60 lbs.	12	40245 (1)	–	40245CRY	6	–	–	29203	29302
30265	18	8-1/4	9	17-1/8	6-3/4	8-1/4	14-1/2	60 lbs.	6	40265 (1)	–	40265CRY	6	–	–	29203	29303
30235*	10-7/8	11	5	10-1/4	10	4-3/4	9	50 lbs.	6	40230 (3)	–	40230CRY	6	30236CRY	6	29203	29302
30260	18	11	10	17	9-1/2	9-3/4	14-3/16	60 lbs.	6	40260 (3)	–	40260CRY	6	–	–	29203	29303
30255	10-7/8	16-1/2	5	9-3/4	15	4-3/4	9	60 lbs.	6	40230 (3)	–	40230CRY	6	–	–	29203	29302
30250* ^{SS}	14-3/4	16-1/2	7	14	14-3/4	6-3/4	12	75 lbs.	6	40245 (3)	41250 (6)	40245CRY	6	–	–	29203	29302
30270	18	16-1/2	11	17-1/8	14-3/4	10-1/4	14	75 lbs.	3	40270 (3)	41270 (6)	40270CRY	6	–	–	29203	29303
30320	8-5/8	33	5	7	31-1/2	4-3/16	6	80 lbs.	4	40321 & 40220 (7)	–	40220CRY	7 / 6	30321	4	–	–

One color per carton: Specify Red, Blue, Yellow, Stone, Clear, Green or Black. Order in carton quantities. CAUTION: When using bins with hanging systems, do not exceed the weight capacity for the rack, which may be less than the total sum of bin capacities. 40321=Full Divider; 40220=Short Divider. *Available in Specialty Colors: Purple and Light Blue. †Available in Additional Colors: SS=Sandstone, TC=Terra Cotta and HG=Hunter Green. ‡()=Max. # of divider slots per bin.

AkroBin Rack & Shelving Systems

Low Profile Floor Rack – Single-Sided		Rack Dimensions (In.)			Bin Dimensions (In.)				Wt. Capacity (Lbs.)	Colors	
Model No.	Description	W	H	D	Bin Model No.	L	W	H	Bin Qty.	Panel/Top	
30650GY	Low Profile Floor Rack	52-5/8	40	13-1/2	–	–	–	–	–	500/250	–
30650GY240	Low Profile Floor Rack	52-5/8	40	13-1/2	30240	14-3/4	8-1/4	7	24	500/250	B, R, Y, SC
30650GY250	Low Profile Floor Rack	52-5/8	40	13-1/2	30250	14-3/4	16-1/2	7	12	500/250	B, R, Y, SC
30650GYASST	Low Profile Floor Rack	52-5/8	40	13-1/2	30240 / 30250	See Above			12 / 6	500/250	B, R, Y, SC
30656GY	Low Profile Floor Rack no Shelf	52-5/8	39-7/8	13-1/2	–	–	–	–	–	500	B, R, Y, SC
30656GY240	Low Profile Floor Rack no Shelf	52-5/8	39-7/8	13-1/2	30240	14-3/4	8-1/4	7	24	500	B, R, Y, SC
30656GY250	Low Profile Floor Rack no Shelf	52-5/8	39-7/8	13-1/2	30250	14-3/4	16-1/2	7	12	500	B, R, Y, SC
30656GYASST	Low Profile Floor Rack no Shelf	52-5/8	39-7/8	13-1/2	30240 / 30250	See Above			12 / 6	500	B, R, Y, SC

Specify color of bins when ordering. B=Blue, R=Red, Y=Yellow, SC=Clear.




30656GY250B

UP TO 250 LBS.

Low Profile Floor Rack – Double-Sided		Rack Dimensions (In.)			Bin Dimensions (In.)				Wt. Capacity (Lbs.)	Colors	
Model No.	Description	W	H	D	Bin Model No.	L	W	H	Bin Qty.	Panel/Top	
30606GY	Low Profile Floor Rack	52-5/8	40	27	–	–	–	–	–	500 per side/250	–
30606GY240	Low Profile Floor Rack	52-5/8	40	27	30240	14-3/4	8-1/4	7	48	500 per side/250	B, R, Y, SC
30606GY250	Low Profile Floor Rack	52-5/8	40	27	30250	14-3/4	16-1/2	7	24	500 per side/250	B, R, Y, SC
30606GYASST	Low Profile Floor Rack	52-5/8	40	27	30240 / 30250	See Above			24 / 12	500 per side/250	B, R, Y, SC
30607GY	Low Profile Floor Rack no Shelf	52-5/8	39-7/8	27	–	–	–	–	–	500	B, R, Y, SC
30607GY240	Low Profile Floor Rack no Shelf	52-5/8	39-7/8	27	30240	14-3/4	8-1/4	7	48	500	B, R, Y, SC
30607GY250	Low Profile Floor Rack no Shelf	52-5/8	39-7/8	27	30250	14-3/4	16-1/2	7	24	500	B, R, Y, SC
30607GYASST	Low Profile Floor Rack no Shelf	52-5/8	39-7/8	27	30240 / 30250	See Above			24 / 12	500	B, R, Y, SC
30606DOLLY	Dolly for 30506 or 30607	53	27-1/2	5-7/8	–	–	–	–	–	3600*	–

Specify color of bins when ordering. B=Blue, R=Red, Y=Yellow, SC=Clear. *Do not exceed weight capacity of Low-Profile Rack.



30606GY240Y

UP TO 500 LBS.

AkroBin Wire Shelving Systems			Bin Dimensions (In.)			Shelf Dimensions (In.)			Quantity	
Model No.	Description	AkroBin Colors	L	W	H	D	L	H	Bins	Shelves
AWS143630320	Wire Shelving w/ 30320 Bins	B, R, Y, G, S, BK, SC	8-5/8	33	5	14	36	74	12	11
AWS143630240	Wire Shelving w/ 30240 Bins	B, R, Y, G, S, BK, SC	14-3/4	8-1/4	7	14	36	74	36	4
AWS143630250	Wire Shelving w/ 30250 Bins	B, R, Y, G, S, BK, SC	14-3/4	16-1/2	7	14	36	74	18	4
AWS184830260	Wire Shelving w/ 30260 Bins	B, R, Y, G, S, BK, SC	18	11	10	18	48	74	24†	6
AWS183630265	Wire Shelving w/ 30265 Bins	B, R, Y, G, S, BK, SC	18	8-1/4	9	18	36	74	18†	5
AWS183630270	Wire Shelving w/ 30270 Bins	B, R, Y, G, S, BK, SC	18	16-1/2	11	18	36	74	9†	5
AWS244830348BE	Mobile Wire Shelving w/ 30348 Bins	BEIGE	20-1/2	8-1/4	7	24	48	74	30	6
AWS2460M30358	Mobile Wire Shelving w/ 30358 Bins	BEIGE	20-1/2	11	7	24	60	68	30	6

Bin color code: R=Red, B=Blue, Y=Yellow, G=Green, S=Stone, BK=Black, SC=Clear. Specify one bin color when ordering. †Bonus bins included.



AWS184830260G

UP TO 2000 LBS.

AkroBin Standard Bin Cabinets

AkroBin Steel Cabinet Packages		
Model No.	Description	Bin Model No. / Qty. of Bins
AC3624Y	36" W x 24" D x 78" H Cabinet w/ Louvered Panels on Back & Doors with 138 Assorted AkroBins	30210YELLO - 48; 30220YELLO - 48; 30230YELLO - 24; 30240YELLO - 12; 30250YELLO - 6
AC3624Y3AS	36" W x 24" D x 78" H Cabinet w/ 3 Shelves, Louvered Panels on Back & Doors with 102 Assorted AkroBins	30210YELLO - 48; 30220YELLO - 48; 30250YELLO - 6
AC3618Y	36" W x 18" D x 78" H Cabinet w/ Louvered Panels on Back Wall, Flush Doors with 42 Assorted AkroBins	30230YELLO - 24; 30240YELLO - 12; 30250YELLO - 6



AC3624Y

UP TO 1500 LBS.



akro-mils.com

1293 South Main Street, Akron, Ohio 44301 • Tel: 800.253.2467 • Fax: 330.761.6348 • sales@akro-mils.com
 In Canada: Ak-West, Inc. • Tel: 877.979.8940 • Fax: 403.225.1696 • sales@ak-westinc.com • ak-westinc.com