

Round Spacer / Wall Thickness 1,2 5,6/8x7 Steel nickel plated

05.65.073

Product No. **05.65.073**

Model	Metal Spacers
Type	Standard, cut ends
Design	Cut
Inner Diameter	for M5- Dia.5.0-6.0
Outer Diameter	8.00 mm
Length	7.00 mm
Material	Steel
Plating	Nickel-plated E2E
Special Features	004T Material
RoHS II compliant	yes
Reach/SVHC free	yes

Similar products

- Round Spacer / Wall Thickness 1,2 5,6/8x7 Steel zinc plated
05.65.071
- Round Spacer / Wall Thickness 2,3 5,3/10x7 Brass nickel plated
05.55.073
- Round Aluminum Spacer/ Wall Thickness = 1,4mm / 5,2/8,0x7
05.75.078

