

Hex-Standoff / Male - Female M3/SW5x5 A=12 Brass nickel plated

05.13.052

Product No. **05.13.052**

Model	Hex Male / Female
Length	5.00 mm
Thread 1 (Female)	M3
Inside Threadlength	2.50 mm
Outside Threadlength	12.00 mm
Material	Brass QQ-B-6261 ASTM-B-16
Plating	Nickel-plated E1E
Wrench Size / Dia.	5 WS / Ø
Thread 2 (Male)	M3
RoHS II compliant	yes
Reach/SVHC free	yes

