



**IP20**  
SUITABILITY



50A  
125/250V AC  
UL/CSA



50A  
3Ø 250V AC  
UL/CSA




50A  
3Ø 480V AC  
UL/CSA

### Plugs

Description	Cord Dia.	Catalog Number		
Nylon cover, thermoplastic polyester interior.	.830"-1.250" (21.08-31.75)	<b>CS6365C</b>	<b>CS8365C</b>	<b>CS8165C</b>

Note: See page B-60 for accessories.




**CS6365C**

### Flanged Inlets

Description	Catalog Number		
Zinc plated steel casing, thermoset interior.	<b>CS6375</b>	<b>CS8375</b>	<b>CS8175</b>
Zinc plated steel casing, thermoset interior with lift cover.	<b>CS6375M2</b>	-	-
Gray Valox® housing and flange.	<b>HBL6375S*</b>	-	-

Note: \*Type 3R.



**CS6375**

**IP20**  
SUITABILITY



50A  
125/250V AC  
UL/CSA



50A  
3Ø 250V AC  
UL/CSA




50A  
3Ø 480V AC  
UL/CSA

### Connector Bodies

Description	Cord Dia.	Catalog Number		
Nylon cover, thermoplastic polyester interior.	.830"-1.250" (21.08-31.75)	<b>CS6364C</b>	<b>CS8364C</b>	<b>CS8164C</b>

Note: See page B-60 for accessories.




**CS6375M2**


### Receptacles

Description	Catalog Number		
Black phenolic.	<b>CS6369</b>	<b>CS8369</b>	<b>CS8169</b>

Note: See page B-60 for accessories.



**CS6364C**



**CS6369**