

IEC Pin and Sleeve Unfused Circuit-Lock® Devices

20, 30, 60 and 100 Ampere – North American Ratings, 32 Ampere – International Rating



IP67
SUITABILITY

Enclosure Type 4X, 12

Rating				Unfused Circuit-Lock® Devices		Reverse Service		
Amps	Poles and Wires	Configuration		AC Voltage	Unfused Circuit-Lock® Devices		Reverse Service	
		Recep.	Plug		Mechanical Interlock	Mating Plug	Mechanical Interlock	Mating Plug
20	3P 4W			120/240V			–	–
	3P 4W			3Ø 240V	HBL420MI9W	HBL420P9W	–	–
	3P 4W			3Ø 480V	HBL420MI7W	HBL420P7W	–	–
	3P 4W			3Ø 600V	HBL420MI5W	HBL420P5W	–	–
30	2P 3W			120V	HBL330MI4W	HBL330P4W	–	–
	2P 3W			240V	HBL330MI6W	HBL330P6W	–	–
	2P 3W			480V	HBL330MI7W	HBL330P7W	–	–
	3P 4W			120/240V	HBL430MI12W	HBL430P12W	–	–
	3P 4W			3Ø 240V	HBL430MI9W	HBL430P9W	HBL430MI9WR	HBL430P9WR
	3P 4W			3Ø 480V	HBL430MI7W	HBL430P7W	HBL430MI7WR	HBL430P7WR
	3P 4W			3Ø 600V	HBL430MI5W	HBL430P5W	HBL430MI5WR	HBL430P5WR
	4P 5W			3ØY 120/208V	HBL530MI9W	HBL530P9W	–	–
	4P 5W			3ØY 277/480V	HBL530MI7W	HBL530P7W	–	–
	4P 5W			3ØY 347/600V	HBL530MI5W	HBL530P5W	–	–
32	3P 4W			380V 50HZ- 440V 60Hz	HBL432MI3W	HBL432P3W	–	–
60	2P 3W			120V	HBL360MI4W	HBL360P4W	–	–
	2P 3W			240V	HBL360MI6W	HBL360P6W	–	–
	2P 3W			480V	HBL360MI7W	HBL360P7W	–	–
	3P 4W			120/240V	HBL460MI12W	HBL460P12W	HBL460MI12WR	HBL460P12WR
	3P 4W			3Ø 240V	HBL460MI9W	HBL460P9W	HBL460MI9WR	HBL460P9WR
	3P 4W			3Ø 480V	HBL460MI7W	HBL460P7W	HBL460MI7WR	HBL460P7WR
	3P 4W			3Ø 600V	HBL460MI5W	HBL460P5W	HBL460MI5WR	HBL460P5WR
	4P 5W			3ØY 120/208V	HBL560MI9W	HBL560P9W	–	–
	4P 5W			3ØY 277/480V	HBL560MI7W	HBL560P7W	–	–
	4P 5W			3ØY 347/600V	HBL560MI5W	HBL560P5W	–	–
100	2P 3W			240V	HBL3100MI6W	HBL3100P6W	–	–
	3P 4W			120/240V	HBL4100MI12W	HBL4100P12W	HBL4100MI12WR	HBL4100P12WR
	3P 4W			3Ø 240V	HBL4100MI9W	HBL4100P9W	HBL4100MI9WR	HBL4100P9WR
	3P 4W			3Ø 480V	HBL4100MI7W	HBL4100P7W	HBL4100MI7WR	HBL4100P7WR
	3P 4W			3Ø 600V	HBL4100MI5W	HBL4100P5W	HBL4100MI5WR	HBL4100P5WR
	4P 5W			3ØY 120/208V	HBL5100MI9W	HBL5100P9W	–	–

Note: 20, 30 and 32A – 1 inch NPT hub supplied; 60 and 100A – 1¼ inch hub supplied.