


MMX-602/SW - Mixer

482 mm
19"



Microphone line mixer, 6 channels.

- 6 stereo line inputs, 6 balanced mono microphone inputs, switchable
- Adjustable automatic talkover (-12 dB), switchable for channel 1 or channels 1+2
- Balance control for each stereo input channel
- 3-way equalizer
- 12 V phantom power can be switched on additionally
- LED VU meter, peak LED
- Master output and record output
- Output can be switched stereo/mono
- Adjustable headphone output
- 482 mm (19") rack installation, 1 RS

Technical Data

Line input, stereo	: 100 mV/10 k Ohm
Microphone input	: 1 mV/6.6 k Ohm
Master output, stereo	: 1 V/600 Ohm
Record output, stereo	: 310 mV/600 Ohm
Headphones, stereo	: ? 8 Ohm
Frequency range	: 20-20,000 Hz
THD	: 0.1 %
S/N ratio	: 62 dB, unweighted
Equalizer, bass	: ±12 dB/50 Hz
Equalizer, midrange	: ±12 dB/1 kHz
Equalizer, treble	: ±12 dB/10 kHz
Power supply	: 230 V~/50 Hz/12 VA
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 482x47x208 mm, 1 RS
Weight	: 2.8 kg
Line input, stereo	: 6 x RCA L/R
Microphone input	: 6 x XLR, bal.
Master output, stereo	: 1 x RCA L/R, 1 x XLR L/R, bal.
Record output, stereo	: 1 x RCA L/R
Headphones	: 1 x 6.3 mm jack