



Class 10 (C10), UHS Speed Class 3 (U3)  
Capacities: SDHC: 16GB, 32GB  
SDXC: 64GB\*\*

## SanDisk Extreme<sup>®</sup> SDHC<sup>™</sup>/SDXC<sup>™</sup> UHS-I cards

The speed and capacity you need to capture 4K Ultra HD<sup>3</sup> video today

### Highlights

- Up to 40MB/s\* write speeds for faster shot-to-shot performance and up to 90MB/s\* for faster transfer
- Highest SD<sup>™</sup> card video recording performance with both Class 10 and UHS Speed Class 3 (U3)<sup>2</sup> ratings for capturing Full HD and 4K Ultra HD (3840 x 2160p) video<sup>3</sup>
- Up to 64GB\*\* capacity for longer video shoots and uninterrupted photo sessions

### Eight times faster than ordinary cards<sup>1</sup>

Up to eight times faster than ordinary memory cards, these cards deliver the video recording performance you need to capture 4K Ultra HD and Full HD video<sup>3</sup>. Shooting at UHS Speed Class 3 (U3)<sup>2</sup>—three times faster than U1—you'll take your videos to a whole new level of resolution, one that looks breathtaking on the new 4K Ultra HD televisions and monitors.

### Capture stunning images and keep them safe

Enjoy extreme continuous shot-to-shot performance up to 40MB/s\* write speed and transfer files fast with read speeds up to 90MB/s\*. Available in storage capacities from 16GB to 64GB\*\*, SanDisk Extreme SDHC/SDXC cards are built for and tested in harsh conditions<sup>4</sup>; temperature proof, water proof, shock proof, and X-ray proof and come with downloadable RescuePRO<sup>®</sup> Deluxe<sup>6</sup> data recovery software to recover accidentally deleted images, so you'll never lose a good day's work.

**SanDisk<sup>®</sup>**

## Technical Specifications

<b>Form factor</b>	SDHC™ (16GB and 32GB), SDXC™ (64GB)
<b>Available capacities</b>	16GB, 32GB, 64GB**
<b>Performance/speed</b>	Up to 90MB/s* read and up to 40MB/s* write speed
<b>Card dimension</b>	0.94" x 1.25" x 0.08" (24 mm x 32 mm x 2.1 mm)
<b>Operating temperature</b>	-13°F to 185°F (-25°C to 85°C)
<b>Storage temperature</b>	-40°F to 185°F (-40°C to 85°C)
<b>Compatibility</b>	Compatible with all SDHC, SDXC, SDHC UHS-I, and SDXC UHS-I supporting host devices
<b>Security</b>	Built-in write-protect switch prevents accidental data loss
<b>Support</b>	Lifetime limited warranty <sup>5</sup>
<b>Includes</b>	RescuePRO® Deluxe data recovery software downloadable offer <sup>6</sup>

**4K**  
ULTRA HD



UHS  
Speed  
Class **3**

CLASS **10**

# SanDisk®

At SanDisk, we're expanding the possibilities of data storage. For more than 25 years, SanDisk's ideas have helped transform the industry, delivering next generation storage solutions for consumers and businesses around the globe.

951 SanDisk Drive | Milpitas | CA 95035 | USA

\* Up to 90MB/s read; up to 40MB/s write speed. Based on internal testing; performance may be lower depending upon host device.  
1MB = 1,000,000 bytes.

\*\* 1GB = 1,000,000,000 bytes. Actual user storage less.

<sup>1</sup> Ordinary cards up to 5MB/s write speed. 1MB = 1,000,000 bytes.

<sup>2</sup> UHS Speed Class 3 designates a performance option designed to support 4K Ultra HD video recording with UHS enabled host devices.

<sup>3</sup> Full HD (1920x1080) and 4K Ultra HD (3840x2160) video support may vary based upon host device, file attributes and other factors. See [www.sandisk.com/HD](http://www.sandisk.com/HD)

<sup>4</sup> See [www.sandisk.com/proof](http://www.sandisk.com/proof) for additional information and limitations.

<sup>5</sup> 30-year warranty in Germany, Canada and regions not recognizing lifetime warranty. See [www.sandisk.com/wug](http://www.sandisk.com/wug)

<sup>6</sup> Registration required; terms and conditions apply.

SanDisk, SanDisk Extreme and RescuePRO Deluxe are trademarks of SanDisk Corporation, registered in the United States and other countries.

The SDHC and SDXC marks and logos are trademarks of SD-3C, LLC.

©2015 SanDisk Corporation. All rights reserved. 6/15