


LCD Vibration Activated Hour Meter With Magnet Mounting Hour Meter, T56 Series

ENM's series T56 LCD Vibration Activated Hour Meter. The hour meter features 6-digits with an hour glass icon as a running indicator. There is a jumper connector on the backside of the unit which can easily be removed in order to activate the hour meter. After removal the unit operates only when it is introduced to vibrating equipment.

This meter can be installed anywhere on equipment with no special wiring connection or power source to operate. There is a magnet on the back for mounting on metal surface. The internal battery supplies all the necessary power for the gauge to operate for years of service. The total operating hours are always shown on the LCD display.

This compact tamper proof meter is 100 % sealed with potting compound on the back side.



T56F6

Specifications

Display Reading:	6-Digits 99999.9 Hours
Display Height:	.196" or [5mm] height (Available in 7mm)
Accuracy:	Better than +/- 0.01% over entire range
Temperature:	Standard -25°C to +70°C (-13°F to +158°F)
Battery Life:	Internal Lithium Battery 8 years plus, non-replaceable
Operation:	Removable jumper connection in the back
Vibration Resistance:	SAE J1378, 20G
Mounting Configuration:	Magnet mounting on back See reverse side for detail


Features

- No External Power Source Required
- Available with 2 alert maintenances
- Totally sealed IP67, even works underwater
- Vibration Activated Detection System
- Unit contains no mercury
- Internal battery provides a display that is always on
- Vibration: SAE J1378, 20G
- Shock: SAE J1378, 55G
- Humidity: SAE J1378, 95% RH
- Quartz Crystal Accuracy
- Made in the U.S.A

2015 ENM Co.®

T56 Series

Dimensional Data



2015 ENM Co.®

LIMITED WARRANTY

ENM Company resettable electromechanical counters are warranted to the consumer to be free from defects in material and workmanship for a period of 1 year. All ENM products which fall within the warranty period due to defects in material or workmanship will be repaired or replaced, at ENM's option, without charge to the consumer when returned with proof of purchase to any authorized ENM dealer in the United States, transportation charges prepaid, provided there is no evidence of improper installation, tampering, or other abuse. All implied warranties, including any implied warranty of merchantability or fitness for a particular purpose, shall be limited in duration to the express warranty period specified above. ENM disclaims any liability for consequential damages due to breach of any written or implied warranty on its products. Datasheet information subject to change.