

## VGA + Audio over Cat5/Cat6 Extender Kit, Transmitter & Receiver with EDID, 2 Local/2 Remote Displays, 1440x900, Up to 500-ft.

MODEL NUMBER: **B130-202A**



### Description

Tripp Lite B130-202A allows you to extend two 1024x768 VGA video signals + Stereo Audio up to 500 ft., over ordinary Cat5e cable, from a single VGA+Audio source. The Transmitter / Receiver kit also features two local VGA HD15 ports, supporting a total of four VGA monitors ( 2 Local and 2 Remote ). Compatibility issues can occur when EDID information is not properly communicated between the source and the display. The B130-202A includes an EDID copy feature which stores a monitor's EDID information in the transmitter and sends it to the source, ensuring optimal compatibility. Supports all operating systems, and is plug-and-play...no software or drivers are required.

### Features

- Connect up to four monitors; 2 local and 2 remote
- 3.5mm Stereo audio support and extension
- Extends a 1440 x 900 @ 60Hz signal up to 165 ft. (50 m) from the source
- Extends a 1024 x 768 @ 60Hz signal up to 500 ft. (150 m) from the source
- EDID copy feature ensures optimal display compatibility
- Built-in equalization control allows for adjustment of the video image
- All operating systems are supported
- Plug-and-play; no software or drivers are required
- HDCP compliant

### Highlights

- Extends a VGA + Stereo Audio signal up to 500 ft.
- Connect up to four VGA monitors: 2 Local and 2 Remote
- EDID copy feature ensures optimal display compatibility

### System Requirements

- PC with VGA video output and 3.5mm Stereo output
- Monitors with VGA input; speakers with 3.5mm Stereo input

### Package Includes

- B130-202A Transmitter Unit
- B130-202A Receiver Unit
- (x2) external power supplies (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Screwdriver for equalization adjustment
- Owner's manual

## Specifications

OVERVIEW	
Display Style	Extender



Cable Type	UTP (Cat5, Cat5e, Cat6, Cat6a); VGA
<b>PHYSICAL</b>	
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	Transmitter: 1.06 x 4.50 x 2.44 Receiver: 1.06 x 4.50 x 2.44
Unit Dimensions (hwd / cm)	Transmitter: 2.69 x 11.43 x 6.2 Receiver: 2.69 x 11.43 x 6.2
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	-4 to 158 (-20 to 70 C)
<b>CONNECTIONS</b>	
Connector A	HARDWIRE
Connector B	HARDWIRE
Ports	2
Local Console Ports	1 x RJ45, 3 x HD15F, 1 x 3.5mm Stereo
Remote Console Port	1 x RJ45, 2 x HD15F, 1 x 3.5mm Stereo
<b>SPECIAL FEATURES</b>	
Chromebook Compatible	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>