

1-Port Plug-n-Play USB 2.0 over Cat5/Cat6 Extender Kit, Transmitter and Receiver, Hi-Speed USB up to 164-ft. (50M)

MODEL NUMBER: **B203-101-PNP**



Description

Tripp Lite's B203-101-PNP, USB 2.0 over Cat5 Extender Kit, allows you to connect your USB-equipped Windows PC to a USB 2.0 or 1.1 peripheral or device up to 164 ft (50 meters) away. This is especially useful for connecting a printer or other peripheral that is far away from your computer, but does not have network connectivity or is located in an area where the network is unavailable. The USB extender kit sends the USB signal from the transmitter to the receiver over a user-supplied Cat5/5e/6 cable. Transfer rates of up to 480Mbps at the maximum length. Compatible with Windows and Mac computerse. Plug and Play...no Drivers or Software required. Backwards compatible with USB 1.1 peripherals. For maximum signal integrity, use Cat5e Solid Conductor UTP cable. The USB extender kit's connectors and internal components are manufactured using high-quality materials suitable for use in demanding office, industrial, and commercial settings. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Connect a Hi-Speed USB 2.0 device up to 164 ft. (50m) from your computer
- Uses readily available Cat5/Cat6 cable
- Includes a 1 ft. USB A/B device cable for connecting the local transmitter unit to a computer
- Supports Hi-Speed data transfer rates up to 480Mbps
- Plug and Play...no Drivers or Software required
- Compatible with Windows and Mac
- Backwards compatible with USB 1.1
- Before using with a touchscreen monitor, first confirm with the monitor manufacturer that USB 2.0 over Cat5 extenders are supported
- RoHS-compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

Highlights

- Connects a USB 2.0 or 1.1 peripheral up to 164 ft. from your Computer
- Plug and Play...no Drivers or Software required
- Windows and MAC compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Use with USB 2.0 peripherals that need to exceed the 16 ft. (5 m) distance limitation

Package Includes

- Local transmitter unit with built-in USB cable
- Remote receiver unit
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's manual



OVERVIEW	
Cable Type	USB; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
Operating Temperature	0 to 40 C (32 to 104 F)
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	RJ45 (FEMALE)
Connector C	USB B (FEMALE)
Connector D	RJ45 (FEMALE)
Ports	1
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>