

Models listed in the main section of this catalog	List of models (models not listed in the main section of this catalog are options. Standards for optional model numbers may differ from the certified standards listed at right.)			Category	Frame Size	Rib	Standard (certification status is for the models listed in this catalog, and standards for optional model numbers may differ.)			page
	Without sensor	With pulse sensor	With PWM speed control function and pulse sensor				UL	CSA	TÜV	
9G0912S201	9G0912S202	9G0912S201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0912S2011	9G0912S2021	9G0912S2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G0924A201	9G0924A202	9G0924A201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0924A2011	9G0924A2021	9G0924A2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G0924G101	9G0924G102	9G0924G101	—	DC	92×92×38mm	Yes	✓	✓	✓	145
9G0924G1011	9G0924G1021	9G0924G1011	—	DC	92×92×38mm	No	✓	✓	✓	145
9G0924H101	9G0924H102	9G0924H101	—	DC	92×92×38mm	Yes	✓	✓	✓	145
9G0924H1011	9G0924H1021	9G0924H1011	—	DC	92×92×38mm	No	✓	✓	✓	145
9G0924H201	9G0924H202	9G0924H201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0924H2011	9G0924H2021	9G0924H2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G0924M201	9G0924M202	9G0924M201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0924M2011	9G0924M2021	9G0924M2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G0924S201	9G0924S202	9G0924S201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0924S2011	9G0924S2021	9G0924S2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G0948A201	9G0948A202	9G0948A201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0948A2011	9G0948A2021	9G0948A2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G0948G101	9G0948G102	9G0948G101	—	DC	92×92×38mm	Yes	✓	✓	✓	145
9G0948G1011	9G0948G1021	9G0948G1011	—	DC	92×92×38mm	No	✓	✓	✓	145
9G0948H101	9G0948H102	9G0948H101	—	DC	92×92×38mm	Yes	✓	✓	✓	145
9G0948H1011	—	9G0948H1011	—	DC	92×92×38mm	No	✓	✓	✓	145
9G0948H201	9G0948H202	9G0948H201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0948H2011	9G0948H2021	9G0948H2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G0948J101	—	9G0948J101	—	DC	92×92×38mm	Yes	✓	✓	✓	145
9G0948J1011	—	9G0948J1011	9G0948P1J031	DC	92×92×38mm	No	✓	✓	✓	145
9G0948M201	9G0948M202	9G0948M201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0948M2011	9G0948M2021	9G0948M2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G0948S201	9G0948S202	9G0948S201	—	DC	92×92×32mm	Yes	✓	✓	✓	135
9G0948S2011	9G0948S2021	9G0948S2011	—	DC	92×92×32mm	No	✓	✓	✓	135
9G1212A401	9G1212A402	9G1212A401	—	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1212A4011	9G1212A4021	9G1212A4011	—	DC	120×120×25mm	No	✓	✓	✓	153
9G1212B401	—	9G1212B401	—	DC	120×120×25mm	Yes	—	—	—	153
9G1212B4011	—	9G1212B4011	—	DC	120×120×25mm	No	—	—	—	153
9G1212E101	9G1212E102	9G1212E101	—	DC	120×120×38mm	Yes	✓	✓	✓	163
9G1212E1011	9G1212E1021	9G1212E1011	—	DC	120×120×38mm	No	✓	✓	✓	163
9G1212E401	9G1212E402	9G1212E401	9G1212P4E05	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1212E4011	9G1212E4021	9G1212E4011	9G1212P4E041	DC	120×120×25mm	No	✓	✓	✓	153
9G1212F101	9G1212F102	9G1212F101	—	DC	120×120×38mm	Yes	✓	✓	✓	163
9G1212F1011	9G1212F1021	9G1212F1011	—	DC	120×120×38mm	No	✓	✓	✓	163
9G1212F401	9G1212F402	9G1212F401	—	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1212F4011	9G1212F4021	9G1212F4011	—	DC	120×120×25mm	No	✓	✓	✓	153
9G1212G101	9G1212G102	9G1212G101	9G1212P1G04	DC	120×120×38mm	Yes	✓	✓	✓	163
9G1212G1011	9G1212G1021	9G1212G1011	9G1212P1G081	DC	120×120×38mm	No	✓	✓	✓	163
9G1212G401	9G1212G402	9G1212G401	9G1212P4G03	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1212G4011	9G1212G4021	9G1212G4011	9G1212P4G031	DC	120×120×25mm	No	✓	✓	✓	153
9G1212H101	9G1212H102	9G1212H101	—	DC	120×120×38mm	Yes	✓	✓	✓	163
9G1212H1011	9G1212H1021	9G1212H1011	—	DC	120×120×38mm	No	✓	✓	✓	163
9G1212H401	9G1212H402	9G1212H401	9G1212P4H04	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1212H4011	9G1212H4021	9G1212H4011	—	DC	120×120×25mm	No	✓	✓	✓	153
9G1212M101	9G1212M102	9G1212M101	—	DC	120×120×38mm	Yes	✓	✓	✓	163
9G1212M1011	9G1212M1021	9G1212M1011	—	DC	120×120×38mm	No	✓	✓	✓	163
9G1212M401	9G1212M402	9G1212M401	—	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1212M4011	9G1212M4021	9G1212M4011	—	DC	120×120×25mm	No	✓	✓	✓	153
9G1224A401	9G1224A402	9G1224A401	—	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1224A4011	9G1224A4021	9G1224A4011	—	DC	120×120×25mm	No	✓	✓	✓	153
9G1224E101	9G1224E102	9G1224E101	—	DC	120×120×38mm	Yes	✓	✓	✓	163
9G1224E1011	9G1224E1021	9G1224E1011	—	DC	120×120×38mm	No	✓	✓	✓	163
9G1224E401	9G1224E402	9G1224E401	9G1224P4E01	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1224E4011	9G1224E4021	9G1224E4011	—	DC	120×120×25mm	No	✓	✓	✓	153
9G1224F101	9G1224F102	9G1224F101	—	DC	120×120×38mm	Yes	✓	✓	✓	163
9G1224F1011	9G1224F1021	9G1224F1011	—	DC	120×120×38mm	No	✓	✓	✓	163
9G1224F401	9G1224F402	9G1224F401	—	DC	120×120×25mm	Yes	✓	✓	✓	153
9G1224F4011	9G1224F4021	9G1224F4011	—	DC	120×120×25mm	No	✓	✓	✓	153