


U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
<b>SKINTOP® DIX</b>		19.11.2014

Easy insertion of several cables into one gland  
Higher packing density allows smaller part construction



Assembly time



Reliability



Temperature-resistant



### Application range

For use in SKINTOP® cable glands.

A sealing ring with several holes is used in place of the inner sealing insert.

### Note

IP 68 can be achieved when all openings are closed and all bores are optimally occupied, i.e. when using cables with nominal diameter and/or SKINTOP® DIX-DV sealing plugs

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Classification:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: plug for cable screw gland
Colour delivered:	natural
Material:	Silicone
Protection rating:	IP 54
Temperature range:	-40°C to +100°C

Product Management	Document: LAPP_PRO1074EN.pdf	1 / 3
--------------------	------------------------------	-------

## SKINTOP® DIX

19.11.2014

Part number	Article designation / size	PG size	Number of cables x clamping range
SKINTOP® DIX			
53607225	DIX 7225	7	2 x 2,5
53607417	DIX 7417	7	4 x 1,7
53609230	DIX 9230	9	2 x 3
53611225	DIX 11225	11	2 x 2,5
53611330	DIX 11330	11	3 x 3
53611240	DIX 11240	11	2 x 4
53611430	DIX 11430	11	4 x 3
53613250	DIX 13250	13.5	2 x 5
53613340	DIX 13340	13.5	3 x 4
53613440	DIX 13440	13.5	4 x 4
53616140	DIX 16140	16	1 x 4
53616225	DIX 16225	16	2 x 2,5
53616240	DIX 16240	16	2 x 4
53616340	DIX 16340	16	3 x 4
53616350	DIX 16350	16	3 x 5
53616440	DIX 16440	16	4 x 4
53616540	DIX 16540	16	5 x 4
53616450	DIX 16450	16	4 x 5
53616356	DIX 16356	16	3 x 5,6
53616260	DIX 16260	16	2 x 6
53616360	DIX 16360	16	3 x 6
53621550	DIX 21550	21	5 x 5
53621460	DIX 21460	21	4 x 6
53621640	DIX 21640	21	6 x 4
53621270	DIX 21270	21	2 x 7
53621370	DIX 21370	21	3 x 7
53621280	DIX 21280	21	2 x 8
53621380	DIX 21380	21	3 x 8
53629556	DIX 29556	29	5 x 5,6
53629470	DIX 29470	29	4 x 7
53629570	DIX 29570	29	5 x 7
53629480	DIX 29480	29	4 x 8
53629290	DIX 29290	29	2 x 9
53629390	DIX 29390	29	3 x 9



Part number	Article designation / size	PG size	Number of cables x clamping range
53629490	DIX 29490	29	4 x 9
53629675	DIX 29675	29	6 x 7,5