


U.I. Lapp GmbH	PRODUCT INFORMATION	
SKINTOP® DIX		07.11.2014

Easy insertion of several cables into one gland
Higher packing density allows smaller part construction



Assembly time



Reliability



Temperature-resistant



Application range

For use in SKINTOP® cable glands.

A sealing ring with several holes is used in place of the inner sealing insert.

Note

IP 68 can be achieved when all openings are closed and all bores are optimally occupied, i.e. when using cables with nominal diameter and/or SKINTOP® DIX-DV sealing plugs

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Classification:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: plug for cable screw gland
Colour delivered:	natural
Material:	Silicone
Protection rating:	IP 54
Temperature range:	-40°C to +100°C

Product Management	Document: LAPP_PRO1074EN.pdf	1 / 3
--------------------	------------------------------	-------

Part number	Article designation / size	PG size	Number of cables x clamping range	Pieces / PU
SKINTOP® DIX				
53607225	DIX 7225	7	2 x 2,5	100
53607417	DIX 7417	7	4 x 1,7	100
53609230	DIX 9230	9	2 x 3	100
53611225	DIX 11225	11	2 x 2,5	100
53611330	DIX 11330	11	3 x 3	100
53611240	DIX 11240	11	2 x 4	100
53611430	DIX 11430	11	4 x 3	100
53613250	DIX 13250	13.5	2 x 5	100
53613340	DIX 13340	13.5	3 x 4	100
53613440	DIX 13440	13.5	4 x 4	100
53616140	DIX 16140	16	1 x 4	50
53616225	DIX 16225	16	2 x 2,5	50
53616240	DIX 16240	16	2 x 4	50
53616340	DIX 16340	16	3 x 4	50
53616350	DIX 16350	16	3 x 5	50
53616440	DIX 16440	16	4 x 4	50
53616540	DIX 16540	16	5 x 4	50
53616450	DIX 16450	16	4 x 5	50
53616356	DIX 16356	16	3 x 5,6	50
53616260	DIX 16260	16	2 x 6	50
53616360	DIX 16360	16	3 x 6	50
53621550	DIX 21550	21	5 x 5	50
53621460	DIX 21460	21	4 x 6	50
53621640	DIX 21640	21	6 x 4	50
53621270	DIX 21270	21	2 x 7	50
53621370	DIX 21370	21	3 x 7	50
53621280	DIX 21280	21	2 x 8	50
53621380	DIX 21380	21	3 x 8	50
53629556	DIX 29556	29	5 x 5,6	50
53629470	DIX 29470	29	4 x 7	50
53629570	DIX 29570	29	5 x 7	50
53629480	DIX 29480	29	4 x 8	50
53629290	DIX 29290	29	2 x 9	50
53629390	DIX 29390	29	3 x 9	50



Part number	Article designation / size	PG size	Number of cables x clamping range	Pieces / PU
53629490	DIX 29490	29	4 x 9	50
53629675	DIX 29675	29	6 x 7,5	50