



Regular Wirestripping Handpiece Model: 10517



Description

Thermal wire stripping is an age-old method of stripping the insulative jacket from your wire with 100% assurance that you are not nicking the conductor. American Beauty offers a complete array of thermal wire stripping systems, hand pieces and elements, sure to meet your specific need.

Features and Benefits

Light-weight, palm-sized hand piece with comfort grip padding minimizes operator fatigue.

Wide variety of Ni-Chrome wire stripping elements are available allowing user to find the perfect fit for their application.

Technical Specifications

User Manual	Download
Connection Type	Tapered Pins
RoHS Compliant	Yes
Country of Origin	US
Package Length	9.50 in / 24.13 cm
Package Width	2.00 in / 5.08 cm
Package Height	2.00 in / 5.08 cm
Shipping Weight	.60 lbs / 0.27 kg
Warranty Policy	Details

Replacement Parts

The following products can be used as replacements for Model 10517 featured on this page:

Model	Product Name	Price
10545	Ni-Chrome Wirestripping Elements (Round, Single Notched)	\$11.40

Accessories

The following products can be used as Accessories for Model 10517 featured on this page:

Model	Product Name	Price
10520	Ni-Chrome Wirestripping Elements (Flat, Double Notched)	\$11.40
10529	Ni-Chrome Wirestripping Elements (Flat, Single Notched)	\$11.40

Similar Products

The following products are related (similar model but different specifications, etc.) to Model 10517 featured on this page:

Model	Product Name	Price
10503	Standard Capacity Wirestripping System	\$496.00