




## 5/64" Steel Electrodes for Resistance Soldering

Model: 10542



American Beauty Tools - Resistance Soldering Replacement Electrodes - Model 10542

### Description

A resistance soldering system is only as good as your 'Point of Contact'. American Beauty incorporates only the highest quality electrodes and elements into our hand pieces. All carbon and stainless steel electrodes are copper-clad for improved current flow, except for Models 10565, 10566, 105134 & 105159 whose short lengths don't require such measures. Inferior quality electrodes and elements will affect overall system performance and could void applicable warranties. (Six Electrodes Per Package)

### Features and Benefits

### Technical Specifications

<b>RoHS Compliant</b>	Yes
<b>User Manual</b>	Download
<b>Tip Configuration</b>	Conical
<b>Tip Diameter</b>	.078125 in
<b>Tip Length</b>	1.5 in / 3.81 cm
<b>Width of Working Area</b>	.02 in / 0.05 cm
<b>Tapered Distance of Working Area</b>	.25 in / 0.64 cm
<b>Understanding Tip Measurements</b>	Explanation
<b>Country of Origin</b>	US
<b>Package Length</b>	2.50 in / 6.35 cm
<b>Package Width</b>	1.00 in / 2.54 cm
<b>Package Height</b>	.125 in / 0.32 cm
<b>Shipping Weight</b>	.01 lbs / 0.00 kg
<b>Warranty Policy</b>	Details

### Similar Products

The following products are related (similar model but different specifications, etc.) to Model 10542 featured on this page:

Model	Product Name	Price
10541	Light Tweezer Style Handpiece	\$148.00