



## 3/32" Probe Style Handpiece Model: 10515



### Description

American Beauty offers the widest selection of resistance soldering handpieces in the world. Our hand pieces are designed and built to provide absolute performance in even the toughest environments. By generating heat instantaneously and right at the point of contact, you are able to easily handle the historically difficult soldering jobs.

### Features and Benefits

**Copper-coated carbon electrodes** can be easily notched/shaped, allowing the user to customize the handpiece to their specific application.

### Technical Specifications

<b>User Manual</b>	Download
<b>Product Length</b>	6 in / 15.24 cm
<b>Electrode Size/Diameter</b>	.094 in / 0.24 cm
<b>Connection Type</b>	Tapered Pins
<b>RoHS Compliant</b>	Yes
<b>Country of Origin</b>	US
<b>Package Length</b>	9.50 in / 24.13 cm
<b>Package Width</b>	2.00 in / 5.08 cm
<b>Package Height</b>	2.00 in / 5.08 cm
<b>Shipping Weight</b>	.40 lbs / 0.18 kg
<b>Warranty Policy</b>	Details

### Replacement Parts

The following products can be used as replacements for Model 10515 featured on this page:

Model	Product Name	Price
10530	3/32" Carbon Electrodes for Resistance Soldering	\$35.20

### Similar Products

The following products are related (similar model but different specifications, etc.) to Model 10515 featured on this page:

Model	Product Name	Price
10508	Ultra-Light Capacity Probe-Style Resistance Soldering System	\$485.00