



Micro Tweezer Style Handpiece

Model: 105133



Description

American Beauty offers the widest selection of resistance soldering handpieces in the world. Our hand pieces are designed and built to provide absolute performance in even the toughest environments. By generating heat instantaneously and right at the point of contact, you are able to easily handle the historically difficult soldering jobs.

Features and Benefits

Ni-Chrome electrodes can be easily bent or notched, allowing the user to customize the handpiece to their specific application.

Technical Specifications

User Manual	Download
Product Length	6 in / 15.24 cm
Opening between Electrodes	.375 in / 0.95 cm
Electrode Size/Diameter	.04 in / 0.10 cm
RoHS Compliant	Yes
Connection Type	Tapered Pins
Country of Origin	US
Package Length	9.50 in / 24.13 cm
Package Width	2.00 in / 5.08 cm
Package Height	2.00 in / 5.08 cm
Shipping Weight	.40 lbs / 0.18 kg
Warranty Policy	Details

Replacement Parts

The following products can be used as replacements for Model 105133 featured on this page:

Model	Product Name	Price
105134	.04" Ni-Chrome Electrodes for Resistance Soldering	\$10.40

Similar Products

The following products are related (similar model but different specifications, etc.) to Model 105133 featured on this page:

Model	Product Name	Price
10599	Micro Capacity Tweezer-Style Resistance Soldering System	\$496.00