

**NEW**



Linkable with the Slimline 5Q5 and 7Q5  
See pages 58-60



## RGBW

### Optics

- 12 x 5W quad-colour LEDs (RGBW)
- Beam angle: 25° (field angle: 40°)
- 400Hz refresh rate

### Control

- DMX channels: 2/3/4 or 7 selectable
- Static colour, colour change, colour fade, auto run, sound active and master/slave modes

### Dimmer

- 0 - 100% dimming and variable strobe

### Additional features

- Bracket allows for multiple rigging or floor standing applications
- 4 push button menu with LCD display
- IEC in/out sockets
- 3-Pin XLR in/out sockets
- Convection cooled

### Specifications

- Power consumption: 70W
- Power supply: 100~240V, 50/60Hz
- Dimensions: 87 x 1018 x 63mm
- Weight: 2.2kg

Order code	Version
LEDJ67	Black housing
LEDJ67A	White housing



Optional IR remote  
Order code: LEDJ90C



Convection cooled,  
no fan!



Optional Twin Case  
Order code: CASE29

## RGBA

### Optics

- 12 x 5W quad-colour LEDs (RGBA)
- Beam angle: 25° (field angle: 40°)
- 400Hz refresh rate

### Control

- DMX channels: 2/3/4 or 7 selectable
- Static colour, colour change, colour fade, auto run, sound active and master/slave modes

### Dimmer

- 0 - 100% dimming and variable strobe

### Additional features

- Bracket allows for multiple rigging or floor standing applications
- 4 push button menu with LCD display
- IEC in/out sockets
- 3-Pin XLR in/out sockets
- Convection cooled

### Specifications

- Power consumption: 70W
- Power supply: 100~240V, 50/60Hz
- Dimensions: 87 x 1018 x 63mm
- Weight: 2.2kg

Order code	Version
LEDJ67B	Black housing
LEDJ67C	White housing



Optional IR remote  
Order code: LEDJ90C



Convection cooled,  
no fan!



Optional Twin Case  
Order code: CASE29

25° RGBW	7725	2280	945	535	335
25° RGBA	7338	2166	897	508	318

