

T-1³/₄ MIDGET FLANGE BASE


SUBMINIATURE NEON LAMP

115V AC RED

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING
WL-A1H	T-1 ³ / ₄	MF	115V AC

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT COLOR / APPEARANCE	LIFE HRS
	MIN	NOM	MAX		
115V AC	—	1.20	—	HIGH BRIGHTNESS RED	25,000

DIMENSIONAL CHARACTERISTICS



NOTES

1. Nickel-plated brass construction base
2. Recommended series resistor 47K Ω 1/4W for 100~125V operation
3. Dark effect reduced
4. Caution: Bulb may shatter and/or circuit may be damaged without external series resistance
5. Part mark WL-A1H
6. RoHS compliant
7. ANSI trade number A1H

