


# T-1<sup>3</sup>/<sub>4</sub> MIDGET FLANGE BASE

## SUBMINIATURE NEON LAMP

115V AC ORANGE

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE	RATING
WL-C7A		T-1 <sup>3</sup> / <sub>4</sub>		MF	115V AC
TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT	LIFE HRS
	MIN	NOM	MAX	COLOR / APPEARANCE	
115V AC	—	.70	—	STANDARD BRIGHTNESS ORANGE	25,000

## DIMENSIONAL CHARACTERISTICS



## NOTES

1. Nickel-plated brass construction base
2. Recommended series resistor  $100\text{K } \Omega$   $\frac{1}{4}\text{W}$  for 100~125V operation
3. Caution: Bulb may shatter and/or circuit may be damaged without external series resistance
4. Park mark WL-C7A
5. RoHS compliant
6. ANSI trade number C7A, NE-2D

