



PRODUCT SPECIFICATION

| | |
|-------------------------|--------------------------|
| Brand | C.K |
| Product Range | Prybar and wrecking bars |
| Catalogue number | 4310 & 4314 |
| Date | 16/08/2007 |

| Range Description Pipe cutters | |  <p style="text-align: center;">T4310</p>  <p style="text-align: center;">T4314</p> | | |
|---|-------------------------|---|----------------|------------|
| Features | | | | |
| <p>T4310</p> <ul style="list-style-type: none"> • Manufactured from forged spring steel for strength and durability • Specially contoured for effective nail pulling and prying • Ends are angle ground giving a chiseling or scraping edge | | | | |
| <p>T4314</p> <ul style="list-style-type: none"> • Goose neck wrecking bars manufactured from high quality octagonal cross section steel • Designed for heavy duty tasks such as levering timber and pulling nails | | | | |
| Item Number | Item Description | EAN No | Commodity code | Carton Qty |
| T4310 | Prybar/nailpuller 380mm | 5013969027822 | 82055910 | 6 |
| T431418 | Wrecking bar 450mm | 5013969069532 | 82055910 | 1 |
| T431424 | Wrecking bar 600mm | 5013969069549 | 82055910 | 1 |

| | |
|------------------------------------|--|
| Technical product information | |
| Standards compliance | None applicable |
| User health and safety information | None applicable |
| RoHS/WEEE compliance | This product range does not fall within the scope of RoHS or WEEE regulations |
| Material safety data | None applicable |
| Warranty | C.K tools are guaranteed for life against imperfect materials or workmanship Normal wear of cutting edges is not covered under the terms of this warranty |
| Country of origin | T4310 – Taiwan T4324 – Great Britain |

Dimensional details

| Item | Product only | | | | Product on primary packaging | | | |
|---------|--------------|----------|-----------|--------------|------------------------------|----------|-----------|----------------|
| | Width mm | Depth mm | Height mm | Net weight g | Width mm | Depth mm | Height mm | Gross weight g |
| T4310 | 35 | 80 | 380 | 626 | 35 | 80 | 380 | 626 |
| T431418 | 30 | 120 | 470 | 849 | 30 | 120 | 470 | 849 |
| T431424 | 30 | 135 | 610 | 1551 | 30 | 135 | 610 | 1551 |

| Item | Shelf box (secondary packaging) | | | | Euro Pallet data Wi x Hi | |
|---------|---------------------------------|----------|-----------|----------------|-----------------------------|---------------------|
| | Width mm | Depth mm | Height mm | Gross weight g | No of cartons on base | Number of rows high |
| T4310 | 110 | 425 | 55 | 3904 | | |
| T431418 | | | | | | |
| T431424 | | | | | | |

Packaging waste details

| Item | Primary Packaging | | | | Secondary packaging | | | |
|---------|-------------------|-----|--------|-----|---------------------|-----|--------|-----|
| | Plastic g | Use | Card g | Use | Plastic g | Use | Card g | Use |
| T4310 | | | | | 30 | Bag | 118 | Box |
| T431418 | | | | | | | | |
| T431424 | | | | | | | | |