

SD02032

## DATA SHEET



### GASCAT 60 TOOL KIT

An engineer's toolkit featuring an Antex Gascat 60 Butane gas powered soldering iron rated nominally at 60watts with an approximate run time of 1 hour on a full tank. The kit also includes a variety of tools, and a digital multimeter. This multi-functional tool is CE approved.

#### **IRON SPECIFICATIONS GASCAT 60**

NOMINAL POWER (W)	60
AVERAGE RUN TIME	1 hour
NOMINAL TIP TEMP (°C)	Adjustable
FITTED BIT	soldering bit (bits for other applications available)
IGNITION	Flint wheel
POWER	Butane gas (lighter fuel)

#### **OTHER TOOLS INCLUDED IN KIT:**

- Pair of mini cutters

- Pair of mini pliers
- Screwdriver - flat blade
- Screwdriver - cross
- Tape measure 2mtr x 16mm
- Auto-lock blade
- Hex Allen Key set 1.5mm-6mm
- Desoldering pump
- 2 meter tube of lead-free solder
- Gascat 60 with flint wheel ignition
- Spare soldering bit
- Digital multimeter with battery
- Hot air tip (for heat shrinking)
- Weight - 780g
- Dimensions - 285 x 180 x 50 mm