

Main

Ampere Rating	200A
Application	Designed for variable depth, flange mounted applications
Approvals	UL Recognized File: E52639 CCN WHTY2 - CSA Certified File: LR44199 Class: 4652 04
Fuse Clip Amperes	200A@250/600V
Fuse Type	Class H, K, J and R
Horsepower Rating	40HP@200VAC - 60HP@230VAC - 125HP@460VAC - 150HP@575VAC - 40HP@250VDC(max)
Includes	Switch, Operating Mechanism and Handle Mechanism (A1)
Maximum Voltage Rating	600VAC
Mounting Type	Flange
Terminal Type	Lugs
Type	T

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.