

JIC-2488 - High Leverage Diagonal Cutter Curved - Data Sheet

Crafted with an angled head for heavy-duty wire cutting in confined spaces, and made of chrome vanadium steel for strength and cutting ability.



Specifications	
Cut Type	Diagonal
Bend Angle	13°
Jaw Length	13/16"
Jaw Thickness	3/8"
Jaw Width	1-3/16" (30.1625mm)
Material	Chrome Vanadium Steel
Color	Red Handle
Length	8" (203mm)
Weight	0.797 lbs
UPC No	811490011946