





# ALLEN® HEX KEYS AND SETS

All hex keys are precision formed to exact dimensional tolerances for precise fit.



Heat treated, tempered alloy steel provides high strength and resistance to rotational distortion.

Molded handle provides better grip and more torque.



Heat treated, tempered alloy steel provides high strength and resistance to rotational distortion.

All hex keys are precision formed to exact dimensional tolerances for precise fit.

## SECTION 15 CONTENTS

Ball-Plus™ Ball End L-Keys, T-Handles and Screwdrivers

Long and Short Arm Hex Keys

Cushion-Grip T- Handles

Duracast® Fold-Ups

Standard Fold-Ups

HI-VIS™ Fold-Ups

Loop Handles

Forged T-Handles

Handi-Hex™ Drivers

Hex Key Sets

Hex Key Assortments



**Ball Plus™ Long Arm Sets**

Product Number	No. Of Keys	Type	Key Sizes Inches
56190	13	caddy - uncarded	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56193	13	caddy - carded	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56195	8	pouch	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32
56196	12	caddy - uncarded	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16
56197	10	pouch	1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4
56198	7	caddy - uncarded	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

**Ball Plus™ Long Arm Sets METRIC**

Product Number	No. Of Keys	Type	Key Sizes mm
56191	9	caddy - carded	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10
56194	9	caddy - uncarded	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10
56199	6	pouch	1.5, 2, 2.5, 3, 4, 5

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

**Ball Plus™ Fractional/Metric Long Arm Combo Set**

Product Number	No. Of Keys	Type	Key Sizes Inches	Key Sizes mm
56192	22	caddy - carded	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 3/8	2, 2.5, 3, 4, 5, 6, 8, 10

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

**Ball Plus™ Individual Long Arm Hex Keys**

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
59300	.050	59312	9/64	59324	3/8
59302	1/16	59314	5/32	59326	7/16
59304	5/64	59316	3/16	59328	1/2
59306	3/32	59318	7/32	59330	9/16
59308	7/64	59320	1/4	59332	5/8
59310	1/8	59322	5/16	59334	3/4

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

**Ball Plus™ Individual Long Arm Hex Keys METRIC**

Product Number	Key Sizes mm	Product Number	Key Sizes mm	Product Number	Key Sizes mm
59100	1.5	59109	4.5	59116	10
59101	1.27	59110	5	59117	11
59102	2	59111	5.5	59118	12
59104	2.5	59112	6	59120	14
59106	3	59113	7	59122	17
59107	3.5	59114	8	59124	19
59108	4	59115	9		

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1



Always wear eye protection when near tools in use.



Ball Plus™ Comfort Grip T-Handle Sets

Product Number	No. Of Keys	Type	Key Sizes Inches	Key Sizes mm
56131	6	pouch	5/32, 3/16, 7/32, 1/4, 5/16, 3/8	
56130	10	pouch	3/32*, 7/64*, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	
56134	11	pouch	5/32, 3/16, 7/32, 1/4, 5/16, 3/8	4, 5, 6, 8, 10

\*Hex End Only  
ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1



Ball Plus™ Comfort Grip T-Handle Sets METRIC

Product Number	No. Of Keys	Type	Key Sizes mm
56133	5	pouch	4, 5, 6, 8, 10
56132	7	pouch	2.5*, 3, 4, 5, 6, 8, 10

\*Hex End Only  
ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

Ball Plus™ Individual Comfort Grip T-Handles

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
57602*	3/32	57610	5/32	57616	1/4
57604*	7/64	57612	3/16	57618	5/16
57606	1/8	57614	7/32	57620	3/8
57608	9/64				

\*Hex End Only  
ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1



Ball Plus™ Individual Comfort Grip T-Handles METRIC

Product Number	Key Sizes mm	Product Number	Key Sizes mm	Product Number	Key Sizes mm
57632*	2.5	57638	5	57642	8
57634	3	57640	6	57644	10
57636	4				

\*Hex End Only  
ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

Ball Plus™ Screwdriver Handle Sets

Product Number	No. Of Keys	Type	Key Sizes Inches
56180	8	pouch	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32
56181	8	roll	7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16
56182	13	pouch	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56183	7	pouch	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

Ball Plus™ Screwdriver Handle Sets METRIC

Product Number	No. Of Keys	Type	Key Sizes mm
56185	6	pouch	1.5, 2, 2.5, 3, 4, 5
56186	7	pouch	1.27, 1.5, 2, 2.5, 3, 4, 5
56187	9	pouch	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1





**Ball Plus™ Screwdriver Handles**

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
57650	.050	57655	1/8	57660	1/4
57651	1/16	57656	9/64	57661	5/16
57652	5/64	57657	5/32	57662	3/8
57653	3/32	57658	3/16	57663	7/16
57654	7/64	57659	7/32	57664	1/2


ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1

**Ball Plus™ Screwdriver Handles**

**METRIC**

Product Number	Key Sizes mm	Product Number	Key Sizes mm	Product Number	Key Sizes mm
57670	1.27	57675	3.5	57680	6
57671	1.5	57676	4	57681	7
57672	2	57677	4.5	57682	8
57673	2.5	57678	5	57683	9
57674	3	57679	5.5	57684	10

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1



**Ball Plus™ Long Length Screwdriver Handle Set**

Product Number	No. Of Keys	Type	Key Sizes Inches
56184	11	pouch	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1

**Ball Plus™ Long Length Screwdriver Handle Set**

**METRIC**

Product Number	No. Of Keys	Type	Key Sizes mm
56188	8	pouch	2, 2.5, 3, 4, 5, 6, 8, 10

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1



**Ball Plus™ Long Length Screwdriver Handles**

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
57750	5/64	57754	9/64	57758	1/4
57751	3/32	57755	5/32	57759	5/16
57752	7/64	57756	3/16	57760	3/8
57753	1/8	57757	7/32		

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1

**Ball Plus™ Long Length Screwdriver Handles**

**METRIC**

Product Number	Key Sizes mm	Product Number	Key Sizes mm	Product Number	Key Sizes mm
57770	2	57773	4	57776	8
57771	2.5	57774	5	57777	10
57772	3	57775	6		

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1





Long Arm Sets — In Plastic Holder


Product Number	No. Of Keys	Key Sizes Inches
56148	7	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16
56152	12	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16
56081	13	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

Fractional/Metric Combo Set

Product Number	No. Of Keys	Key Sizes Inches	Key Sizes mm
56009	22	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	1.5, 2, 2.5, 3, 4, 5, 8, 10

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1



Individual Long Arm Hex Keys

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
58007	.035	58014	3/16	58028	5/8
58003	.050	58016	7/32	58030	3/4
58001	1/16	58018	1/4	58032	7/8
58002	5/64	58020	5/16	58034	1
58004	3/32	58022	3/8	58036	1-1/4
58005	7/64	58023	7/16	58038	1-1/2
58006	1/8	58024	1/2	58040	1-3/4
58010	9/64	58026	9/16	58042	2
58012	5/32				

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1



Individual Long Arm Hex Keys METRIC

Product Number	Key Sizes mm	Product Number	Key Sizes mm	Product Number	Key Sizes mm
58048	0.9	58056	3	58066	10
58049	1.3	58058	4	58068	12
58050	1.5	58060	5	58090	14
58052	2	58062	6	58092	17
58054	2.5	58064	8	58094	19

ASME B18.3.2M

TORX® Individual Long Arm

Product Number	Key Sizes Torx	Product Number	Key Sizes Torx
58926	T-10	58929	T-25
58927	T-15	58930	T-27
58928	T-20	58931	T-30

Torx® is a registered trademark of CAMCAR, Division of TEXTRON, Inc.





**Short Arm Sets — In Plastic Holder**

Product Number	No. Of Keys	Type	Key Sizes Inches
56080	13	uncarded	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56108	12	uncarded	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1

**Short Arm Set — In Plastic Holder**

**METRIC**

Product Number	No. Of Keys	Key Sizes mm
56008	9	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10

ASME B18.3.2M



**Individual Short Arm Hex Keys**

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
57002	.028	57018	9/64	57032	1/2
57004	.035	57020	5/32	57034	9/16
57006	.050	57022	3/16	57036	5/8
57008	1/16	57024	7/32	57038	3/4
57010	5/64	57026	1/4	57040	7/8
57012	3/32	57028	5/16	57042	1
57013	7/64	57030	3/8	57044	1-1/4
57014	1/8	57031	7/16	57046	1-1/2

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1

**Individual Short Arm Hex Keys**

**METRIC**

Product Number	Key Sizes mm	Product Number	Key Sizes mm	Product Number	Key Sizes mm
57129	0.7	57122	3	57133	12
57131	0.9	57124	4	57134	14
57135	1.3	57126	5	57138	17
57116	1.5	57128	6	57142	19
57118	2	57130	8	57143	22
57120	2.5	57132	10		

ASME B18.3.2M



**TORX® Individual Short Arm Hex Keys**

Product Number	Key Sizes Torx	Product Number	Key Sizes Torx	Product Number	Key Sizes Torx
57981	T-6	57986	T-15	57991	T-40
57982	T-7	57987	T-20	57992	T-45
57983	T-8	57988	T-25	57993	T-50
57984	T-9	57989	T-27	57994	T-55
57985	T-10	57990	T-30		

Torx® is a registered trademark of CAMCAR, Division of TEXTRON, Inc.



**Comfort-Grip T-Handle Sets — In Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Inches	Overall Length, Inches
56161	8	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	6
56164	8	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	9

**Comfort-Grip T-Handle Set — In Vinyl Pouch METRIC**

Product Number	No. Of Keys	Key Sizes mm	Overall Length, Inches
56093	5	2.5, 3, 4, 5, 6	6



**Comfort-Grip T-Handle Sets — With Metal Stand**

Product Number	No. Of Keys	Key Sizes Inches	Overall Length, Inches
56064	10	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	6
56163	10	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	9



**Individual Comfort-Grip T-Handles**

Product Number	Key Sizes Inches	Overall Length, Inches
57300	3/32	6
57302	7/64	6
57304	1/8	6
57306	9/64	6
57308	5/32	6
57310	3/16	6
57312	7/32	6
57314	1/4	6
57316	5/16	6
57318	3/8	6
58250	3/32	9
58252	7/64	9
58254	1/8	9
58256	9/64	9
58258	5/32	9
58260	3/16	9
58262	7/32	9
58264	1/4	9
58266	5/16	9
58268	3/8	9

**Individual Comfort-Grip T-Handles METRIC**

Product Number	Key Sizes mm	Overall Length, mm
57842	2.5	150
57844	3	150
57846	4	150
57848	5	150
57850	6	150





**DURACAST® Fold-Ups**

Product Number	No. Of Keys	Key Sizes Inches	Handle Length Inches
56346	9	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16	3-1/2
56347	9	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	4-1/4

**DURACAST® Fold-Up METRIC**

Product Number	No. Of Keys	Key Sizes mm	Handle Length Inches
56349	7	1.5, 2, 2.5, 3, 4, 5, 6	3-1/2



**DURACAST® TORX® Fold-Up**

Product Number	No. Of Keys	Key Sizes Torx	Handle Length Inches
56348	7	T-10, T-15, T-20, T-25, T-27, T-30, T-40	4-1/4

Torx® is a registered trademark of CAMCAR, Division of TEXTRON, Inc.




**DURACAST® Ball End Fold-Up**

Product Number	No. Of Keys	Key Sizes Inches	Handle Length Inches
56382	9	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	4-1/4



**DURACAST® Hex Key/Screwdriver Fold-Up**

Product Number	No. Of Keys	Key Sizes mm	Handle Length Inches
56384	6	2, 4, 5, 6 Phillips screwdriver blade Slotted screwdriver blade	4-1/4



**DURACAST® 3 Piece Fold-Up Set 56357 — In Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes			Handle Length Inches
		Inches	mm	Torx	
56346	9	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16			3-1/2
56349	7		1.5, 2, 2.5, 3, 4, 5, 6		3-1/2
56348	7			T-10, T-15, T-20, T-25, T-27, T-30, T-40	4-1/4








**Standard Fold-Ups**

Product Number	Type	No. Of Keys	Key Sizes Inches	Handle Length Inches
56066	uncarded	9	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16	3-3/8
56321	carded	9	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16	3-3/8
56114	uncarded	8	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32	3
56314	carded	8	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32	3
56067	uncarded	9	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	3-3/4
56316	carded	9	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	3-3/4




**Standard Fold-Ups METRIC**

Product Number	Type	No. Of Keys	Key Sizes mm	Handle Length Inches/mm
56070	uncarded	7	1.5, 2, 2.5, 3, 4, 5, 6	3-3/4 (95mm)
56360	carded	7	1.5, 2, 2.5, 3, 4, 5, 6	3-3/4 (95mm)


**Standard HI-VIS™ Fold-Ups**

Product Number	Type	No. Of Keys	Key Sizes Inches	Handle Length Inches
56073	uncarded	9	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16	3-3/8
56391	carded	9	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16	3-3/8
56115	uncarded	8	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32	3
56393	carded	8	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32	3



**Standard HI-VIS™ Fold-Ups METRIC**

Product Number	Type	No. Of Keys	Key Sizes mm	Handle Length Inches/mm
56076	uncarded	7	1.5, 2, 2.5, 3, 4, 5, 6	3-3/4 (95mm)
56395	carded	7	1.5, 2, 2.5, 3, 4, 5, 6	3-3/4 (95mm)




**Long Fold-Ups**

Product Number	Type	No. Of Keys	Key Sizes Inches	Handle Length Inches
56068	uncarded	5	3/16, 7/32, 1/4, 5/16, 3/8	6-3/8
56320	carded	5	3/16, 7/32, 1/4, 5/16, 3/8	6-3/8
56318	carded	9	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	6-3/8




**Long Fold-Ups METRIC**

Product Number	Type	No. Of Keys	Key Sizes mm	Handle Length Inches/mm
56072	uncarded	5	4, 5, 6, 8, 10	6-3/8 (162mm)
56362	carded	5	4, 5, 6, 8, 10	6-3/8 (162mm)




**Long HI-VIS™ Fold-Ups**

Product Number	Type	No. Of Keys	Key Sizes Inches	Handle Length Inches
56074	uncarded	9	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	3-3/4
56394	carded	9	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4	3-3/4



**Long HI-VIS™ Fold-Ups METRIC**


Product Number	Type	No. Of Keys	Key Sizes mm	Handle Length Inches
56077	uncarded	5	4, 5, 6, 8, 10	3-3/4
56396	carded	5	4, 5, 6, 8, 10	3-3/4



**TORX® Fold-Ups**

Product Number	Type	No. Of Keys	Key Sizes Torx	Handle Length Inches
56896	uncarded	7	T-10, T-15, T-20, T-25, T-27, T-30, T-40	3-3/4
56323	carded	7	T-10, T-15, T-20, T-25, T-27, T-30, T-40	3-3/4

Torx® is a registered trademark of CAMCAR, Division of TEXTRON, Inc.



**TORX® HI-VIS™ Fold-Ups**

Product Number	Type	No. Of Keys	Key Sizes Torx	Handle Length Inches
56897	uncarded	7	T-10, T-15, T-20, T-25, T-27, T-30, T-40	3-3/4
56392	carded	7	T-10, T-15, T-20, T-25, T-27, T-30, T-40	3-3/4

Torx® is a registered trademark of CAMCAR, Division of TEXTRON, Inc.



**6" Hex Key Set in Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Inches
56034	9	5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1

**12" Hex Key Set in Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Inches
56110	7	5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1





Individual 6" Hex Keys

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
58070	5/64	58078	3/16
58072	3/32	58080	7/32
58073	7/64	58082	1/4
58074	1/8	58020	5/16
58075	9/64	58086	3/8
58076	5/32		

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1



Individual 12" Hex Keys


Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
58200	5/64	58208	3/16
58202	3/32	58210	7/32
58204	1/8	58212	1/4
58206	5/32		

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

Long Arm Set — In Metal Box

Product Number	No. Of Keys	Key Sizes Inches
56128	13	1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1



Long Arm Set — In Metal Box METRIC

Product Number	No. Of Keys	Key Sizes mm
56085	10	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10, 12

ASME B18.3.2M1

Short Arm Sets — In Metal Box

Product Number	No. Of Keys	Key Sizes Inches
56028	15	.028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56026	18	.028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2, 9/16, 5/8

ASME B18.3 Fed'I Spec. GGG-K-275 AMED 1

Short Arm Sets — In Metal Box METRIC

Product Number	No. Of Keys	Key Sizes mm
56038	12	0.7, 0.9, 1.3, 1.5, 2, 2.5, 3, 4, 6, 8, 10
56036	15	0.7, 0.9, 1.3, 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10, 12, 14, 17

ASME B18.3.2M





**Long Arm Sets — In Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Inches
56150	11	.050, 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56013	13	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56014	15	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2, 9/16, 5/8, 3/4

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1

**Long Arm Sets — In Vinyl Pouch METRIC**


Product Number	No. Of Keys	Key Sizes mm
56018	9	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10
56083	15	0.9, 1.3, 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10, 12, 14, 17, 19

ASME B18.3.2M

**TORX® Long Arm Set — In Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Torx
56900	6	T-10, T-15, T-20, T-25, T-27, T-30

Torx® is a registered trademark of CAMCAR, Division of TEXTRON, Inc.



**Short Arm Sets — In Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Inches
56100	6	.028, .035, .050, 1/16, 5/64, 3/32
56004	7	5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4
56122	9	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4
56030	11	.050, 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56032	15	.028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8
56011	20	.028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1

**Short Arm Set — In Vinyl Pouch METRIC**

Product Number	No. Of Keys	Key Sizes mm
56015	9	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10

ASME B18.3.2M

**TORX® Short Arm Set — In Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Torx
56901	13	T-7, T-8, T-9, T-10, T-15, T-20, T-25, T-27, T-30, T-40, T-45, T-50, T-55

Torx® is a registered trademark of CAMCAR, Division of TEXTRON, Inc.



**Individual 6" Loop Handle Hex Keys**

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
57320	3/32	57325	3/16
57321	7/64	57326	7/32
57322	1/8	57327	1/4
57323	9/64	57328	5/16
57324	5/32	57329	3/8

**Individual 6" Loop Handle Hex Keys METRIC**

Product Number	Key Sizes mm	Product Number	Key Sizes mm
57860	2	57864	5
57861	2.5	57865	6
57862	3	57866	8
57863	4	57867	10



**Individual 9" Loop Handle Hex Keys**

Product Number	Key Sizes Inches	Product Number	Key Sizes Inches
58270	3/32	58275	3/16
58271	7/64	58276	7/32
58272	1/8	58277	1/4
58273	9/64	58278	5/16
58274	5/32	58279	3/8

**Individual 9" Loop Handle Hex Keys METRIC**

Product Number	Key Sizes mm	Product Number	Key Sizes mm
58280	2	58284	5
58281	2.5	58285	6
58282	3	58286	8
58283	4	58287	10





**6" Loop Handle Sets — In Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Inches
56257	8	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4
56255	10	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8

**6" Loop Handle Sets — In Vinyl Pouch METRIC**

Product Number	No. Of Keys	Key Sizes mm	Key Length mm
56261	5	2.5, 3, 4, 5, 6	152
56259	8	2, 2.5, 3, 4, 5, 6, 8, 10	152





**9" Loop Handle Sets — In Vinyl Pouch**

Product Number	No. Of Keys	Key Sizes Inches
56258	8	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4
56256	10	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8

**9" Loop Handle Sets — In Vinyl Pouch METRIC**

Product Number	No. Of Keys	Key Sizes mm	Key Length mm
56262	5	2.5, 3, 4, 5, 6	229
56260	8	2, 2.5, 3, 4, 5, 6, 8, 10	229



**Individual PLAS-T-KEY®**

Product Number	Key Sizes Inches	Key Length Inches
57500	3/32	1-7/8
57502	7/64	2-1/8
57504	1/8	2-5/16
57506	9/64	2-1/2
57508	5/32	2-11/16
57510	3/16	3-3/32
58412	7/32	4-1/2
58414	1/4	4-1/2
58400	3/32	4-1/2
58402	7/64	4-1/2
58404	1/8	4-1/2
58406	9/64	4-1/2
58408	5/32	4-1/2
58410	3/16	4-1/2
58416	5/16	4-1/2
58418	3/8	4-1/2

**Individual PLAS-T-KEY® METRIC**

Product Number	Key Sizes mm	Product Number	Key Sizes mm
57830	2	57836	4
57832	2.5	57838	5
57834	3	57840	6

Torx® is a registered trademark of CAMCAR, Division of TEXTRON, Inc.



**PLAS-T-KEY SET® — With Metal Stand**

Product Number	No. Of Keys	Key Sizes Inches	Key Length Inches
56112	10	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	6

\*Metal stand not sold separately




### Individual HANDI-HEX™ Drivers

Handi-Hex Drivers are designed for general use and production assembly operations using socket screw products. Versatile drivers feature adjustable, replaceable Allen Bits. Each handle identified by bit size. Includes key for bit change or adjustment.

Product Number	Key Sizes Inches	Key Length Inches	Product Number	Key Sizes Inches	Key Length Inches
57400	.028	2	57410	3/32	3
57402	.035	2	57412	7/64	3
57404	.050	3	57414	1/8	3
57406	1/16	3	57416	9/64	3
57408	5/64	3			

ASME B18.3 Fed'l Spec. GGG-K-275 AMED 1



### Replacement Straight Bits

Product Number	Key Size Inches	Key Length Inches	Product Number	Key Size Inches	Key Length Inches
57900	.028	2	57926	1/8	3
57902	.035	2	57201	1/8	5
57904	.050	3	57932	9/64	3
57906	1/16	3	57203	9/64	5
57908	1/16	6	57205	5/32	5
57910	5/64	3	57942	5/32	6
57912	5/64	6	57207	3/16	6
57914	3/32	3	57209	7/32	6
57197	3/32	5	57211	1/4	6
57918	3/32	6	57213	5/16	7
57920	7/64	3	57215	3/8	7
57199	7/64	5			





**Hex Key Assortment 56882**

An assortment of 9 popular sizes of hex keys.

Contains 270 wrenches.

Key Size Inches	Quantity In Box	Key Size Inches	Quantity In Box
5/64	50	7/32	25
3/32	50	1/4	25
1/8	50	5/16	10
5/32	25	3/8	10
3/16	25		



**Hex Key Assortment 56890**

**METRIC**

An assortment of 7 popular metric hex keys.

Contains 175 keys.

Key Size mm	Quantity In Box	Key Size mm	Quantity In Box
1.5	25	4	25
2	25	5	25
2.5	25	6	25
3	25		





