



ADTR

Specifications and dimensions

- Time delay Class CC fuse link
- Cylindrical
- For small motor protection



Features	
Barrel Length	38mm
Barrel Width	10mm
Standards	UL Listed
	CSA Certified
Rated Voltage	600V AC
	300V DC
IR	200kA AC
	100kA DC
Ratings (amperage)	1 to 30A
Operating Temperature	,-55°C to +125°C

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>