











Number of contacts

40+

250 V
10 A

Identification	Wire cross section (mm²)	Part number		Drawing	
		male	female	Dimensions in mm	
Terminal Block Connectors, Screw terminal, Left hand version, Multi contour (MK), silver plated contacts, contact resistance ≤4 mOhm 	0.2–2.5	09 21 040 4601	09 21 040 4701		
Terminal Block Connectors, Screw terminal, Left hand version, Single contour (SK), silver plated contacts, contact resistance ≤4 mOhm 	0.2–2.5	09 21 040 4602	09 21 040 4702		
					
					

Han AV