

## FPF



**Article Number:** 251-10609

**Grommet, Panel Thickness 0.256"-0.319", PE, Natural, 82ft/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** FPF

**Type** G51PF

**Color** Natural (NA)

**Features and Benefits**

- Can be cut to length with scissors, eliminating waste and keeping stock to a minimum.
- Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.

**Product Description** HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.

**Short Description** Grommet, Panel Thickness 0.256"-0.319", PE, Natural, 82ft/pkg

### Product Dimensions

**Length L (Imperial)** 82.0 ft

**Reel Length (imperial)** 9.7 ft

**Variant** Open

**Width W (Imperial)** 0.449 "

**Width W (Metric)** 11.4 mm

**Width W2 (Imperial)** 0.327 "

**Width W2 (Metric)** 8.3 mm

**Height H (Imperial)** 0.268 "

**Height H (Metric)** 6.8 mm

**Height H2 (Imperial)** 0.189 "

**Height H2 (Metric)** 4.8 mm

**Panel Thickness Max. (Imperial)** 0.319 "

**Panel Thickness Max. (Metric)** 8.10 mm

**Panel Thickness Min. (Imperial)** 0.256 "

**Panel Thickness Min. (Metric)** 6.50 mm

### Logistics and Packaging

**Quantity Per** reel

**Package Quantity** 82.0 ft

**Package Quantity (Metric)** 25 m

**Carton Quantity** 1 Reel

**Weight (Metric)** 0.7 kg

## Material and Specifications

---

<b>Material</b>	Polyethylene (PE)
<b>Material Shortcut</b>	PE
<b>Flammability</b>	UL94 HB
<b>Halogenfree</b>	Yes
<b>Operating Temperature</b>	-22°F to +176°F (-30°C to +80°C)
<b>ROHS Compliant</b>	Yes