

SNP1010C2



Article Number: 190-00045

Snapper Hose Clamps, .569"/.651" Min/Max Diameter, POM, White, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number SNP1010C2

Type SNP10

Color White (WH)

Features and Benefits

- Designed for quick, ratcheted installation and can be released and reused.
- Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.

Product Description HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

Short Description Snapper Hose Clamps, .569"/.651" Min/Max Diameter, POM, White, 100/pkg

Product Dimensions

Fixation Method Plug-in mounting

Variant Closed

Width W2 (Imperial) 0.235 "

Width W2 (Metric) 5.97 mm

Diameter Min. (Imperial) 0.569 "

Diameter Min. (Metric) 14.45 mm

Diameter Max. (Imperial) 0.651 "

Diameter Max. (Metric) 16.54 mm

Wall Thickness WT (Imperial) 0.068 "

Wall Thickness WT (Metric) 1.7 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 4000

Material and Specifications

Material Polyacetal (POM)

Material Shortcut POM

Flammability UL94 HB

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

