

## SNP10GHS0C2



**Article Number:** 192-10100

**Snapper Hose Clamps, .571"/.654" Min/Max Diameter, PA66GF13%, Black, 100/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** SNP10GHS0C2

**Type** SNP10

**Color** Black (BK)

**Features and Benefits**

- Designed for quick, ratcheted installation and can be released and reused.
- Heat stabilized material is suitable for high temperature applications.

**Product Description** HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

**Short Description** Snapper Hose Clamps, .571"/.654" Min/Max Diameter, PA66GF13%, Black, 100/pkg

### Product Dimensions

**Fixation Method** Plug-in mounting

**Variant** Closed

**Width W2 (Imperial)** 0.232 "

**Width W2 (Metric)** 5.89 mm

**Bundle Diameter Min. (Imperial)** 0.56 "

**Bundle Diameter Min. (Metric)** 14.5 mm

**Bundle Diameter Max. (Imperial)** 0.65 "

**Bundle Diameter Max. (Metric)** 16.6 mm

**Diameter Min. (Imperial)** 0.571 "

**Diameter Min. (Metric)** 14.5 mm

**Diameter Max. (Imperial)** 0.654 "

**Diameter Max. (Metric)** 16.61 mm

**Nominal Diameter (Imperial)** 5/8 "

**Nominal Diameter (Metric)** 16 mm

**Wall Thickness WT (Imperial)** 0.069 "

**Wall Thickness WT (Metric)** 1.8 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 100 Pieces

**Carton Quantity** 100 Pieces

**Weight (Metric)** 0.24 kg

## Material and Specifications

---

<b>Material</b>	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
<b>Material Shortcut</b>	PA66GF13
<b>Flammability</b>	UL94 HB
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>ROHS Compliant</b>	Yes