

## SNP1GHS0C2



**Article Number:** 192-10010

**Snapper Hose Clamps, .237"/.263" Min/Max Diameter, PA66GF13%, Black, 100/pkg**



Download spec sheet

### Base Data

**Local Order Number** SNP1GHS0C2

**Type** SNP1

**Color** Black (BK)

**Features and Benefits**

- Designed for quick, ratcheted installation and can be released and reused.
- Heat stabilized material is suitable for high temperature applications.

**Product Description** HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

**Short Description** Snapper Hose Clamps, .237"/.263" Min/Max Diameter, PA66GF13%, Black, 100/pkg

### Product Dimensions

**Fixation Method** Plug-in mounting

**Variant** Closed

**Width W2 (Imperial)** 0.149 "

**Width W2 (Metric)** 3.78 mm

**Bundle Diameter Min. (Imperial)** 0.3 "

**Bundle Diameter Min. (Metric)** 6.0 mm

**Bundle Diameter Max. (Imperial)** 0.27 "

**Bundle Diameter Max. (Metric)** 6.8 mm

**Diameter Min. (Imperial)** 0.237 "

**Diameter Min. (Metric)** 6.02 mm

**Diameter Max. (Imperial)** 0.263 "

**Diameter Max. (Metric)** 6.68 mm

**Nominal Diameter (Imperial)** 1/4 "

**Nominal Diameter (Metric)** 6 mm

**Wall Thickness WT (Imperial)** 0.04 "

**Wall Thickness WT (Metric)** 1.0 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 100 Pieces

**Carton Quantity** 100 Pieces

**Weight (Metric)** 0.12 kg

## Material and Specifications

---

<b>Material</b>	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
<b>Material Shortcut</b>	PA66GF13
<b>Flammability</b>	UL94 HB
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>ROHS Compliant</b>	Yes