

T50MR0M4



Article Number: 113-05002

Screw Mount Tie, 50 lb 8.5" Long, Max Bundle Diameter 1.8", #10 Screw, PA66HS, Black, 1,000/pkg



Download spec sheet

Base Data

Local Order Number T50MR0M4

Type T50MR

Color Black (BK)

Features and Benefits

- Mount design secures firmly with any #10 Screw.
- Screw mount style creates low insertion and high extraction force.

Product Description Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.

Short Description Screw Mount Tie, 50 lb 8.5" Long, Max Bundle Diameter 1.8", #10 Screw, PA66HS, Black, 1,000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225 N

Length L (Imperial) 8.5 "

Length L (Metric) 215.0 mm

Fixation Method fixing hole

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.18 "

Width W (Metric) 4.7 mm

Height H (Imperial) 0.22 "

Height H (Metric) 5.7 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 1.8 "

Bundle Diameter Max. (Metric) 45.0 mm

Mounting Hole Diameter D (Imperial) 0.21 "

Mounting Hole Diameter D (Metric) 5.4 mm

Thickness T (Imperial) 0.05 "

Mounting Hole Diameter D Max. 5.4 mm

(Metric) Mounting Hole Diameter D Min. (Metric) 5.4 mm

Thickness T (Metric) 1.2 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000
Carton Quantity	5000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Certification/Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes