


1/2" 1/4"


carolus



- 1/2" 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 mm
 75 mm
 125 mm
 250 mm
 1/2" □ x 5/16" ○

- 1/4" 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
 TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
 4 - 5 - 6 - 8 mm
 5,5 mm
 PH 2 PZ 2
 50 mm
 100 mm


1/2"	12,5	Code	Art.-No.	mm	998
1/4"	6,3	1517023	5899.70	480 x 160 x 50	5014



- 1/2" 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 mm
 75 mm
 125 mm
 250 mm
 1/2" □ x 5/16" ○

- 1/4" 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
 TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
 4 - 5 - 6 - 8 mm
 5,5 mm
 PH 2 PZ 2
 50 mm
 100 mm

1/2"	12,5	Code	Art.-No.	mm	998
1/4"	6,3	1517007	5899.35	480 x 160 x 50	5028



- 1/2" 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 mm
 75 mm
 125 mm
 250 mm
 1/2" □ x 5/16" ○

- 1/4" 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
 TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
 4 - 5 - 6 - 8 mm
 5,5 mm
 PH 2 PZ 2
 50 mm
 100 mm

1/2"	12,5	Code	Art.-No.	mm	998
1/4"	6,3	1516906	5800.00	480 x 160 x 50	4990

