



## DCS355D2

### 18V XR Brushless Oscillating Multi-Tool

#### Selling Proposition

- DEWALT Brushless Motor delivers up to 57% more run time over brushed motors
- QUICK-CHANGE Accessory System allows blades and attachments to be changed quickly without the use of tools
- DUAL-GRIP Variable Speed Trigger provides the ultimate speed and application control
- Bright LED light illuminates dark work surfaces for accurate cutting
- Depth Control Straight Cut Guide increases cutting accuracy for detailed work
- Dust Extraction Adaptor supports use with DEWALT dust extraction vacuums

#### Standard Equipment

- 2 x 2Ah XR Li-Ion battery packs with state of charge indicator
- Multi-Voltage XR Charger
- 1 x TStak Kitbox
- 1 x 31 x 43mm Fast Cut Wood Blade
- 1 x 31 x 43mm Wood with Nails Blade

#### Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Battery chemistry	XR Li-Ion
Voltage	18 V
Battery Capacity	2 Ah
Power Output	300 Watt
Oscillations per Minute	0-20,000
Switch type	Variable Dual Grip
Tool free Accessory Fitment	Yes
Length	310 mm