

PROSAFE ALUMINIUM POCKET INSPECTION LIGHT



- » 220 Lumen white Samsung SMD LEDs
- » Strong die cast aluminium body
- » Convenient pocket clip
- » Rubberised micro switch operation
- » Iron alloy within the pocket clip
- » Protective housing for LEDs
- » Evenly dispersed smooth light spread
- » 2 stage dimming and 8Hz defence strobe

3-6
HOURS
RUNTIME

10
METRE
BEAM RANGE

220
LUMENS
OUTPUT

IP54
DUST & WATER
RESISTANCE

BATTERY 3 x AAA Batteries (included)

WEIGHT 125g with batteries

DIMENSION 162 x 30 x 16mm



RUBBERISED MICRO SWITCH



9 HIGH POWERED SMD LEDs



CONVENIENT POCKET CLIP



SMOOTH EVEN LIGHT SPREAD

