

**SlimLine spanners. Tools to get to grips with. CrV steel drop forged, carefully**

**hardened and plated. With clearly readable sizes.**

**10 year guarantee**

For full professional use!



**DIN  
ISO**



**8-piece SlimLine - double ring spanner set. Including holder. To DIN 838 and ISO 3318.**

Sizes 6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19 and 20 x 22mm.

Each spanner has a clearly marked place for storage. The plastic holder also offers holes to allow for fixing it to a wall.

**NO 23 810** set

Each spanner has a clearly marked place for storage. The plastic holder also offers holes to allow for fixing it to a wall.



PROXXON INDUSTRIAL		SlimLine double ring spanners, individually				
	S <sub>1</sub> x S <sub>2</sub>	B <sub>1</sub>	B <sub>2</sub>	L	H	
23 868	5 x 5,5 mm	9	10	162	5	
23 870	6 x 7 mm	10	12	173	5,6	
23 872	8 x 9 mm	13	14	182	6,1	
23 874	10 x 11 mm	16	17	200	7,9	
23 876	12 x 13 mm	18	19	212	8,5	
23 878	10 x 13 mm	16	19	212	8,5	
23 880	14 x 15 mm	21	23	225	9,8	
23 882	16 x 17 mm	24	25	245	10,4	
23 886	18 x 19 mm	27	28	260	11,3	
23 888	17 x 19 mm	25	28	216	11,3	
23 890	20 x 22 mm	30	32	285	12,8	
23 892	21 x 23 mm	31	33	310	12,9	
23 896	24 x 27 mm	34	38	335	13,9	
23 900	30 x 32 mm	42	45	375	15,3	

