

Type: Female connector 90° with 5 rows

Termination: Press-fit

Number of contacts: 55

Pitch: 2 mm


Operational current: 1.5 A

Packaging: Tray

Standard: IEC 61076-4-101



Technical Specifications on page 204



Accessories

- Processing tools p. 318

Mating connector / Application:

Type C Male connector (p. 238)



Press-fit - Performance level II •••

No. of contacts	Description	Part number
55	without shielding	244-31000-15
55	with shielding	244-31300-15
–	lower shield	244-31600-1

On request

- other contact surface
- also in THTR