

XTL™ 300

DYMO®

24 mm PC-Connected Handheld Industrial Label Maker

- Life-like on screen print preview and colour display shows exactly how labels will look when applied to cables, pipes, panels, and more
- Built-in label applications make getting started from the home screen easy
- Pre-loaded label templates create labels 3x faster* and ensure perfect formatting to save time
- Pre-set layouts for almost 100 patch panel models eliminate size and spacing guesswork
- Prints 6 mm up to 24 mm durable labels including continuous length tape, laminated wire/cable wraps, heat-shrink tubes and pre-sized labels
- Maximised print area helps reduce label waste
- PC-connectivity** and free DYMO ID software for easy transfer of labels to and from the XTL 300 for jobsite editing and printing
- Durable built-in cutter for fast label production
- Impact-resistant rubber bumpers and wipe-clean keypad withstand harsh environments
- Handheld design and contoured finger grips for easy handling
- On-screen label indicator automatically detects and displays the loaded label

*When compared to creating labels on an XTL label maker without templates

** Works with Windows® 7 and later



XTL 300 Single Unit Includes:

- DYMO XTL 300 Label Maker
- All-Purpose Vinyl Label Cartridge, Black on White, 24 mm x 7 mm
- AC Charging Adapter
- USB Cable
- Rechargeable Lithium Polymer Battery
- Lanyard
- Quick Start Guide
- Software Download Guide



XTL 300 Kit Includes (everything in single unit as well as):

- Carrying Case
- Laminated Wire/Cable Wrap Cartridge, Black on White, 21 mm x 39 mm



Quick Specs

Unit Dimensions (H x W x L)	68.58 x 119.38 x 264.16 mm
Weight (excluding battery)	1.13 kg
PC Compatible	Yes, via USB
Accepts Label Sizes	6, 9, 12, 19, 24 mm
Tape Platform	XTL
Resolution	300 dpi
Printing System	Thermal Transfer
Barcodes	Code 128 (Auto), Code 39, Code 39 Mod 43, EAN 8, EAN 13, UPC-A, Codabar, PDF-417, QR Code
Cutter Type	Manual, Replaceable
Power Supply	Lithium Polymer Rechargeable Battery or AC Adapter
Memory	40 MB
Compatibility	Windows® 7 and later
Adapter	Yes
Networking	No
Warranty	3+1 Year Limited
Country of Origin	China

DISTRIBUTED BY:
Newell Europe Sàrl
Chemin de Blandonnet 10
1214 Vernier – Switzerland
WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A **Newell Rubbermaid** Brand

©2015 Newell Europe LLC

XTL™ 300



Item Number	Description		Length (mm)	Width (mm)	Height (mm)	Weight (kg)	QTY	UPC
1873228	DY XTL 300 PRINTER QWERTY UK/IRE	Unit	192	81	293	1.72	1	3501178723281
		Shelf	295	230	350	5.92	1	-
		Case	295	230	350	5.92	3	13501178723288
		Pallet	1200	800	1200	256.50	36	-
1873305	DY XTL 300 PRINTER KIT QWERTY UK/IRE	Unit	408	89	365	2.82	1	3501178733051
		Shelf	440	300	400	9.37	1	-
		Case	440	300	400	9.37	3	13501178733058
		Pallet	1200	800	1200	150.73	12	-

XTL 300 | Compatible Labels

All-Purpose Vinyl

- Moisture, chemical and UV resistance makes vinyl ideal for indoor/outdoor use
- Wide range of colours that fit with OSHA, ANSI and ISO colour standards to enhance workplace communication and safety
- UL recognised as a component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 60°C

Flexible Cable Wrap

- For labelling wires, cables and rounded surfaces, flexible nylon material is designed to conform and stick
- Tear-proof material resists damage when pulled through tight spaces or conduits
- UL recognised as a component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 60°C

Laminated Wire/Cable Wraps

- Pre-sized wire/cable wraps with laminated overwrap protect printed areas from oil, chemicals, moisture, abrasion and fading
- Also available in sheet label formats for high-volume installations
- UL recognised as a component to UL 969
- Temperature Rating: -40°C to 60°C

Permanent Flat Surface

- For labelling panels, blocks, faceplates, shelves, bins, beams and more
- For labelling flat surfaces, a glossy finish leaves a professional look
- UL recognised as a component to UL 969
- Temperature rating: -40°C to 60°C
- RoHS compliant

Heat-Shrink Tube (Continuous)

- Heat-Shrink Tubes provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio
- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL- 23053/5 (Class 1 & 3)
- UL recognised as a component to UL 224
- RoHS compliant
- Temperature rating: Max 125°C

Pre-Sized Labels

- Ideal for flat surface labeling like barcodes, faceplates, shelves, bins, beams and more
- Pre-Sized labels help facilitate batch label printing to improve productivity
- UL recognised as a component to UL 969
- Temperature rating: -40°C to 60°C

DISTRIBUTED BY:
Newell Europe Sàrl
Chemin de Blandonnet 10
1214 Vernier – Switzerland
WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *Newell Rubbermaid* Brand

©2015 Newell Europe LLC

XTL™ 300



XTL 300 Compatible Labels

Width	Length	A	A	A	A	A	A	A	A	A	A	A	A	A
All-Purpose Vinyl														
12 mm	7 m	1868741	1868746	1868751	1868756	1868761	1868766	1868771	1868776	1868781	1868786	1868791	1868796	1868801
19 mm	7 m	1868742	1868747	1868752	1868757	1868762	1868767	1868772	1868777	1868782	1868787	1868792	1868797	1868802
24 mm	7 m	1868743	1868748	1868753	1868758	1868763	1868768	1868773	1868778	1868783	1868788	1868793	1868798	1868803
Permanent Flat Surface														
6 mm	9.1 m	1868738	-	1868735	-	-	-	-	-	-	-	-	-	-
9 mm	9.1 m	1868739	-	1868736	-	-	-	-	-	-	-	-	-	-
12 mm	9.1 m	1868740	-	1868737	-	-	-	-	-	-	-	-	-	-
Flexible Cable Wrap														
12 mm	5.5 m	-	-	1868806	-	-	-	-	-	-	-	-	-	-
19 mm	5.5 m	-	-	1868807	-	-	-	-	-	-	-	-	-	-
24 mm	5.5 m	-	-	1868808	-	-	-	-	-	-	-	-	-	-
Heat-Shrink Tube (continuous)														
6 mm	2.7 m	-	-	1868809	-	-	-	-	-	-	-	-	-	-
12 mm	2.7 m	-	-	1868810	-	-	-	-	-	-	-	-	-	-
24 mm	2.7 m	-	-	1868811	-	-	-	-	-	-	-	-	-	-

XTL 300 Compatible Pre-Sized Labels

SKU	Label Width	Label Length	Labels/Cartridge	Color
Pre-Sized Labels				
1868665	12 mm	12 mm	250	A
1868666	12 mm	25 mm	250	A
1868667	12 mm	38 mm	185	A
1868669	9 mm	25 mm	250	A
1868670	12 mm	19 mm	250	A
1868701	19 mm	25 mm	250	A
Laminated Wire/Cable Wrap				
1868704	21 mm	21 mm	250	A
1868705	21 mm	39 mm	150	A
1868706	21 mm	102 mm	75	A

DISTRIBUTED BY:
 Newell Europe Sàrl
 Chemin de Blandonnet 10
 1214 Vernier – Switzerland
 WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A *Newell Rubbermaid* Brand
 ©2015 Newell Europe LLC

XTL™ 300

Part Number table – Language / Keyboard Type:

DYMO XTL 300 24mm Label Maker Kit, QWERTY, UK/IRE – 1873305

DYMO XTL 300 24mm Label Maker Kit, QWERTZ, DE/AT/CH – 1873308

DYMO XTL 300 24mm Label Maker Kit, AZERTY, FR/BE – 1873481

DYMO XTL 300 24mm Label Maker Kit, QWERTY, SEU+NL - 1873488

