



element 14













SVR Rocker Switches

Industrial - Rated IP68



Newark/ Element 14
www.newark.com

Manufacturer: Eaton
www.eaton.com/VCBU

POSITION	Lens	ROCKER BASE	COMPLETE ASSEMBLY	CIRCUIT DESIGN
ON-OFF	ON Part # 28-7893 OFF Part # 28-7893-2			2 Position, 2 pole On/ On Note: for On/ Off function simply do not wire to Off position
		Eaton Cat. #: SA4SLL4XXXXXLP		
START-STOP	START Part # 28-7893-5 STOP Part # 28-7893-6 :			2 Position, 2 pole On/ On Note: for On/ Off function simply do not wire to Off position
		Eaton Cat. #: SA4SLL4XXXXXLP		
UP-DOWN	UP Arrow Part # 28-7893-10 Down Arrow Part # 28-7893-11 :			3 Position, 2 Pole Momentary On/ Off (center)/ Momentary Off
		Eaton Cat. #: SF4SLL4XXXXXLP		
LOCK-UNLOCK	LOCK Symbol Part # 28-7893-8 UNLOCK Symbol Part # 28-7893-9			2 Position, 2 pole On/ On
		Eaton Cat. # SA4SLL4XXXXXLP:		
AUTO-MAN	AUTO Part # 28-7893-12 MANUAL Part # 28-7893-13 :			2 Position, 2 pole On/ On
		Eaton Cat. #: SA4SLL4XXXXXLP		
HIGH-LOW	HIGH Part # 28-7893-14 LOW Part # 28-7893-15			2 Position, 2 pole On/ On
		Eaton Cat. #: SA4SLL4XXXXXLP		

Call for Quick Quote - No Minium Order on Custom Switches !
1-800-463-9275 or email: customswitches@newark.com

SVR Rocker Switches



element 14

Industrial - Rated IP68



Newark/ Element 14
www.newark.com

Manufacturer: Eaton
www.eaton.com/VCBU

Lens + Rocker Cover + Rocker Base = Complete Assembly

<p>Lens Green Lens : #28-5415 Amber Lens : # 28-55415-2 Red Lens : # 28-5415-3 Blue Lens : # 28-5415-4 White Lens : # 28-5415-5</p>	<p>Custom Lenses Custom Lenses can be printed. Contact your salesperson for details. or email: customswitches@newark.com</p>	<p>Bases - see Below</p>	<p>SVR Connector used to plug wire harnesses into before connecting to SVR # 25-13936</p>
<p>Rocker Bases Part #</p>	<p>Description</p>	<p>Rocker Bases Part #</p>	<p>Description</p>
<p>SARSXX1XXXXXXXXXX</p>	<p>3 position - 2 pole On/ On Non-Illuminated</p>	<p>SFRSXX1XXXXXXXXXX</p>	<p>3 position - 2 pole Mom. On/ Off/ Mom. On Non-Illuminated</p>
<p>SDRSXX1XXXXXXXXXX</p>	<p>3 position - 2 pole On/ Off/ On Non-Illuminated</p>	<p>SFRSXX5XXXXXXXXXX</p>	<p>3 position - 2 pole Mom. On/ Off/ Mom. On Paddle Non-Illuminated</p>
<p>SHRSXX1XXXXXXXXXX</p>	<p>3 position - 2 pole Mom. On/ Off/ Maint. On Non-Illuminated</p>	<p>SMRSXX1XXXXXXXXXX</p>	<p>2 position - 2 pole Mom. On/ Maint. On Non-Illuminated</p>
<p>SA4SLL4XXXXXXLP</p>	<p>2 position - 2 pole On/ On Illuminated</p>	<p>SF4SLL4XXXXXXLP</p>	<p>3 position - 2 pole Mom. On/ Off/ Mom. On Illuminated</p>
<p>SM4SLL4XXXXXXLP</p>	<p>2 position - 2 pole Mom. On/ Maint. On Illuminated</p>	<p>SH4SLL4XXXXXXLP</p>	<p>3 position - 2 pole Mom. On/ Off/ Maint. On Illuminated</p>
<p>SD4SLL4XXXXXXLP</p>	<p>3 position - 2 pole On/ Off/ On Illuminated</p>		

Call for Quick Quote - No Minium Order on Custom Switches !
1-800-463-9275 or email: customswitches@newark.com