



Schneider Electric USA
1415 South Roselle Road
Palatine, IL 60067
Customer Care Center: 1-888-778-2733
Web: www.schneider-electric.us

ITEM # ZB5AVM1, BASE & LIGHT MODULE

Base & Light Module

| Specifications | |
|--------------------------------------------|-----------------------------|
| Product Description | Base & Light Module |
| Ampere Rating | N/A |
| Terminal Type | Screw Clamp |
| Wire Range | min: 1x0.22; max: 2x16AWG |
| Tightening Torque | 0.8 Nm |
| Light Module Electrical Consumption | 24V = 18mA; 120/240V = 14mA |
| CE | Yes |
| RoHS | Yes |
| Contact Configuration | n/a |
| Contact Material | n/a |
| Light Module Supply Voltage | 230-240Vac |
| Light Module Type | LED(white) |
| Light Module Voltage | 230-240Vac |
| Utilization Category | n/a |
| Used On | ZB5 Plastic Operators |
| Application | n/a |