

Product availability: Stock - Normally stocked in distribution facility

Price\*: 173.00 USD

## NATO products



### Main

|                               |   |
|-------------------------------|---|
| Commercial Status             | Commercialised  |
| Range of product              | 9050JCK   |
| Product or component type     | Timer   |
| [In] rated current            | 10 A  |
| Switch function               | DPDT  |
| Contacts type and composition | 2 NO + 2 NC   |
| Control circuit voltage       | 120 V AC  |
| Maximum switching voltage     | 240 V AC  |
| Mounting support              | Socket  |
| Pin number                    | 11  |
| Shape of pin                  | Tubular   |
| Product certifications        | CE<br>CSA<br>UL listed  |
| Time delay type               | Off-delay<br>On-delay<br>Interval<br>One shot<br>Repeat cycle               |
| Time delay range              | 1...999 min<br>1...999 s<br>0.05...9.99 s<br>0.1...99.9 s<br>0.1...99.9 min |

### Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 21652 - 9050 JCK60, 70 PROGRAMMABLE TIMERS        |
| Discount Schedule     | CP2   |
| GTIN                  | 00785901053880                                    |
| Nbr. of units in pkg. | 1   |
| Package weight(Lbs)   | 0.28  |
| Product availability  | Stock - Normally stocked in distribution facility |
| Returnability         | Y   |
| Country of origin     | US  |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Not Green Premium product   |
| RoHS                     | Compliant - since 0703 - <a href="#">Schneider Electric declaration of conformity</a> |

### Contractual warranty

|        |           |
|--------|-----------|
| Period | 18 months |
|--------|-----------|