

# Product data sheet

## Characteristics

# 9080GM6

## TERMINAL BLOCK 600V 30AMP NEMA +OPTIONS

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1.80 USD

### Main

Commercial Status	Commercialised
Range of product	9080G
Product or component type	Terminal block standard
[In] rated current	30 A
Product certifications	CE CSA UL listed
Material	Tin plated brass busbar Nylon block
Colour	Natural
Quantity per set	Set of 50
[Ue] rated operational voltage	600 V AC
Mounting support	35 mm DIN rail 9080GH track
Product compatibility	GM6B
Electrical connection	Box lugs zinc plated steel
Protection type	Fingersafe DIN 57470
AWG gauge	22...10 AWG copper
Number of terminal blocks	51 per foot

### Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	00785901743927
Nbr. of units in pkg.	50
Package weight(Lbs)	0.90
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0847 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------