

Schroff


EuropacPRO kit, light design, unshielded, for backplane mounting

Catalog Number: 24564-433



- Aluminum construction
- Subrack with side panel type L ("light") with firmly fixed 19" brackets
- Rear horizontal rails for backplane mounting with insulation strip
- Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1
- IP 20, in accordance with IEC 60529
- Modifications such as cutouts, different finishes or dimensions available
- Supplied as space-saving flat-pack
- Horizontal rail type "light"

Other Views



Description

Load:

Minimal

Shock/vibration:

Minimal

Design:

EuropacPRO, Light

EMC Shielding:

- Retrofitable
- Unshielded

Type:


Subrack Kit

Note:

Subrack is not prepared for shielding

Delivery Comprises:

Item	Quantity	Description
1	2	Side panel type L, Al, 2 mm, passivated, with built-in 19" support bracket
2a	2	Front horizontal rail (L-KD)
2c	1	Rear horizontal rail centre (H-ST)
2b	2	Rear horizontal rail (L-ST)
3	6	Threaded inserts, front and rear (pre-fitted)
4	4	Insulation strip (pre-fitted)
5	1	Fixing materials kit, user manual



D = overall depth, $D1$ = insertion depth, $D2$ = board depth = $D1 - 15$ mm










Rear horizontal rail for backplane mounting with insulation strip

Technical Data

Catalog Number	24564-433
Depth mm	295.0
Height U	6.0
Width HP	84.0
Depth D mm	295.0
Depth D1 mm	175/235/295

Accessories

Item		
	Perforated rail for connector according to EN 60603-2 (DIN 41612), 84 HP, with thread M2.5, PU 4 pieces	20822-048
	19" fixing material kit (screw, washer, nut), (8 x screws, 8 x plastic washers, 8 x cage nuts)	21100-435
	ESD clip for guide rails, Spring steel, tin-plated, silver, PU 50 pieces	24560-255
	Guide rails, standard, 160 mm deep, PBT, UL 94 V-0, red, groove width 2 mm, PU 10 pieces	24560-351
	Guide rails, standard, 220 mm deep, PBT, UL 94 V-0, red, groove width 2 mm, PU 10 pieces	24560-353
	Cover plate standard, 160 mm deep, Al, 1.2 mm, perforated, to push into light horizontal rail, PU 2 pieces	24561-051
	Cover plate standard, 220 mm deep, Al, 1.2 mm, perforated, to push into light horizontal rail, PU 2 pieces	24561-052