

# Carolprene® Jacketed Type SOOW

90°C, 600 Volt, Non-UL Portable Cord

**Product Construction:**

**Conductors:**

- 8 through 2 AWG fully annealed stranded bare copper

**Insulation:**

- Premium-grade, color-coded 90°C EPDM
- Color code: See chart below

**Jacket:**

- Carolprene®, black
- Temperature range: -40°C to +90°C

**Jacket Marking:**

- CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA

**Applications:**

- Portable tools and equipment
- Temporary and portable power
- Motors and associated machinery

**Features:**

- Excellent resistance to oil and moisture
- Good tensile strength, elongation and aging characteristics
- High flexibility
- Excellent abrasion resistance
- Ozone-, sunlight (UV)- and weather-resistant
- Water-resistant\*

**Industry Approvals:**

- MSHA Approved
- RoHS Compliant

**Packaging:**

- 250' (76.2 m), 500' (152.4 m), 1000' (304.8 m)
- Other put-ups available on special order

\* Suitable for immersion in water if properly sealed and terminated.

**COLOR CODE CHART**

NO. OF CONDUCTORS	COLOR
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green
5	Black, White, Red, Green, Orange



**TYPE SOOW, NON-UL – 600 VOLT**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(S)</sup>	STD. CTN.
				INCHES	mm	INCHES	mm			
01811*	2	8	65/26	0.050	1.27	0.660	16.76	40	278	250'
01812	3	8	65/26	0.050	1.27	0.695	17.65	40	343	250'
01827	4	8	65/26	0.050	1.27	0.760	19.30	35	442	250'
98267	5	8	65/26	0.050	1.27	0.840	21.34	28	542	250'
01825	3	6	101/26	0.050	1.27	0.790	20.07	55	482	250'
01824	4	6	101/26	0.050	1.27	0.865	21.97	45	599	250'
98270	5	6	101/26	0.050	1.27	0.945	24.00	36	750	250'
01823*	2	4	119/25	0.050	1.27	0.870	22.09	70	515	250'
01822	3	4	119/25	0.050	1.27	0.925	23.49	70	683	250'
01821	4	4	119/25	0.050	1.27	1.015	25.78	60	851	250'
98463	5	4	119/25	0.050	1.27	1.115	28.32	48	1039	250'
01819	3	2	133/.0211	0.055	1.40	1.085	27.56	95	1003	250'
01818	4	2	133/.0211	0.055	1.40	1.170	29.72	80	1248	250'
98187	5	2	133/.0211	0.055	1.40	1.390	35.31	64	1684	250'

\* Non-stock item; minimum quantity purchase required.

† Green conductor for grounding only. Ampacities based on NEC Table 400.5(A)(1).

<sup>(S)</sup> Actual shipping weight may vary.