

100m Infrared Illuminator

Model: VSIR28W60D

Product Overview

High-performance IR illuminator for all lighting conditions. The VSIR28W60D has 12pcs high power IR LED with 100m IR distance. It is IP66 rated with tempered glass panel and aluminum die-casting housing, suitable for indoor or outdoor use.



| Model: VSIR28W60D | |
|-----------------------|------------------------|
| LED Type | 12pc high power IR LED |
| IR Distance | 100m |
| Beam Angle | 60° |
| Day / Night | Auto switch |
| Ingress Protection | IP66 |
| Power Input | 12VDC |
| Power Consumption | 28W |
| Dimensions (WxDxH) | 221x90x232mm |
| Weight | 1.7KG |
| Operating Environment | -30° ~ 50°C |


Product specifications and images are subject to change.

Illuminator Compatibility

This illuminator is compatible with most camera range including: VIP Vision, Securview, Securview Victory Series and Watchguard.



Product Diagram



Your professional CCTV surveillance dealer: