

WSA-24T - Wireless Speaker Adaptor



Wireless stereo transmitter, 2.4 GHz, for audio streaming.

- Matching the receiver WSA-24R
- Stereo/mono selector switch
- LED for indicating status and peak
- Interference-free operation due to FHSS technology (Frequency Hopping Spread Spectrum)
- Analogue line level input via 6.3 mm jacks L/R and 3-pole XLR L/R
- Metal housing
- Power supply via supplied plug-in PSU

djmagazin.de 99

"This set is perfectly suitable for fast and wireless audio transmissions. It features a sophisticated design of neat workmanship. I also like the magnets and the strap which allow for a quick and easy attachment of the receiver. Overall, an excellent set which is available at a favourable price and should definitely be part of any accessory kit."

SOUNDCHECK 02/2016

"All too typical for IMG STAGELINE: the requirements of stage applications are effectively implemented."

tools4music 01/2016

"This compact solution is an excellent aid for every audio supplier ... shows itself ... as a robust and easy-to-use solution for audio streaming."

Technical Data

Frequency range	: 20-20,000 Hz
THD	: < 0.3%
Channel separation	: ≥ 90 dB
Bluetooth	: -
Operating range	: > 30 m with clear view
Profiles	: -
Power supply	: via suppl. PSU
Dimensions	: 130 x 54 x 130 mm
Width	: 130 mm
Height	: 54 mm
Depth	: 130
Weight	: 470 g
Connections	: Inputs: 1 x 6.3 mm stereo jack L/R, analogue 1 x 3-pole XLR L/R, analogue
Other features	: 2.4 GHz, 25 channels, latency: 18 ms