



## Hard Wired 170 Series



### Features

- Single winding, does not provide isolation, for use where equipment is already isolated and only voltage change is required.
- Flexible world wide applications, 50 or 60 Hz. operation, step down (230VAC to 115 VAC) or step up (115VAC to 230VAC).
- Connection by flexible leads, 8" minimum length.
- Models 170A, 170B, 170C & 170D are CSA certified (209651)
- Remember - These units do NOT convert line frequency



Part No.	Capacity	Overall Dimensions					Weight
	VA	A	B	C	D	E	Lbs
<b>170</b>	50	2.19	2.63	2.63	1.75	1.56	2
<b>170A</b>	100	2.50	3.00	3.10	2.00	1.90	3
<b>170B</b>	200	3.13	3.50	3.80	2.50	2.20	4.5
<b>170C</b>	300	3.13	4.00	3.80	2.50	2.70	6
<b>170D</b>	500	3.75	4.50	4.60	3.00	3.30	10
<b>170E</b>	750	3.75	5.50	4.60	3.00	4.30	14
<b>170F</b>	1000	3.75	5.50	4.60	3.00	4.30	14.5
<b>170G</b>	1500	4.38	6.60	5.30	3.50	5.10	22
<b>170J</b>	2000	4.38	6.60	5.30	3.50	5.10	23

*Data subject to change without notice*