

Printview: Ferrule; sleeve for 0.75 mm² / awg 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-222

Ferrule; sleeve for 0.75 mm² / awg 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90

Item No.: 216-222



Ferrule; sleeve for 0.75 mm² / awg 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	216-222
GTIN / EAN	4017332277440
Content	1
Order amount	1,000
Customer item number	

Notes

Technical data

Miscellaneous

Color	gray
Strip length 1	8 mm / 0.31 in
Fire load [MJ]	0.001 [MJ]
Weight [g]	0.079 [g]
Diameter [mm]	3.3 [mm]
Diameter 1 [mm]	2.8 [mm]
Diameter 2 [mm]	1.3 [mm]
Length [mm]	12 [mm]

Printview: Ferrule; sleeve for 0.75 mm² / awg 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-222

Technical data


Length 1 [mm]

6 [mm]

Printview: Ferrule; sleeve for 0.75 mm² / awg 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-222

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.